

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356
<https://www.phoenixcontact.com/us/products/1411356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector set, number of positions: 10, material: PA, connection method: Screw connection, connection cross section: AWG 20- 14

Commercial data

Item number	1411356
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF63
Product key	AF7AFX
GTIN	4046356929264
Weight per piece (including packing)	252.8 g
Weight per piece (excluding packing)	250.6 g
Customs tariff number	85366990
Country of origin	CN

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Set consists of

HC-EVO-D15-HHFS-PL-BK - Housing

1411340

<https://www.phoenixcontact.com/us/products/1411340>



Sleeve housing D15, for single locking latch, material: PA 6.6-FR, cable outlets: 1, straight/lateral, height: 65.5 mm, cable gland: none, Standard

HC-D-G-M20-PLRBK - Cable gland

1411350

<https://www.phoenixcontact.com/us/products/1411350>



EVO plastic cable gland with bayonet locking, for housing series D, size M20, cable diameter: 7 mm ... 13 mm.

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

HC-EVO-D15-BWS-PLR-BK - Housing

1411336

<https://www.phoenixcontact.com/us/products/1411336>



Panel mounting base D15, with single locking latch, material: PA 6.6-FR, height: 26 mm, cable gland: none, Standard, with flat gasket

HC-A10-I-UT-M - Contact insert

1585294

<https://www.phoenixcontact.com/us/products/1585294>



Contact insert, number of positions: 10+PE, size: D15, number of connections per position: 1, Pin, Screw connection, 250 V, 16 A, 0.5 mm² ... 2.5 mm²

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set




1411356

<https://www.phoenixcontact.com/us/products/1411356>

HC-A10-I-UT-F - Contact insert

1585304

<https://www.phoenixcontact.com/us/products/1585304>



Contact insert, number of positions: 10+PE, size: D15, number of connections per position: 1, Socket, Screw connection, 250 V, 16 A, 0.5 mm² ... 2.5 mm²

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Technical data

Product properties

Product type	Connector set
Housing type	Complete housing
Series	HC-D
Type	D15
Number of positions	10
Connection profile	10+PE
No. of cable outlets	1
Protective cover	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	3


Electrical properties

Rated voltage (III/3)	250 V
Rated surge voltage	4 kV
Rated current	20 A

Connection data

Connection method	Screw connection
Connection technology	Screw connection
Conductor cross section	0.5 mm ² ... 2.5 mm ² (applies to stranded conductors with ferrules) 0.5 mm ² ... 2.5 mm ² (applies to stranded conductors with ferrules)
Connection cross section AWG	20 ... 14
Tightening torque	0.5 Nm ... 1.7 Nm (Fixing screws for panel mounting base)
Stripping length	8 mm

Dimensions

Dimensional drawing	
Width	39 mm
Height	100.5 mm
Length	82 mm
Drill hole distance, horizontal	70 mm
Drill hole distance, vertical	17.5 mm

Installation dimensions

Width of the assembly cutout	24 mm
------------------------------	-------

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Length of the assembly cutout	58 mm
-------------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
	CR
Housing material	PA
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PA
Locking latch material	PA

Cable/line

External cable diameter	7 mm ... 13 mm
-------------------------	----------------

Mechanical properties

Mechanical data

Locking type	Latch
--------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 100 °C

Mounting

Assembly note	Connectors may only be actuated when there is no load/voltage.
---------------	--

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set




1411356

<https://www.phoenixcontact.com/us/products/1411356>


Drawings

Dimensional drawing



Mounting cutout

Dimensional drawing



Dimensional drawing


HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Schematic diagram




Pin assignment, connection side, pin left, socket right

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>



Derating diagram

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411356>

DNV

Approval ID: TAE000037S



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Classifications

ECLASS

ECLASS-13.0	27440113
ECLASS-15.0	27440113

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-EVO-A10UT-BWS-HH-M20-PLRBK - Connector set



1411356

<https://www.phoenixcontact.com/us/products/1411356>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	69542a51-7204-4812-bae4-c6a554e89a17

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com