

# MCC-MT 0,2-0,35 - Crimp contact



1859988

<https://www.phoenixcontact.com/us/products/1859988>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Female contact, is inserted into the plug after crimping the conductor, for the module plug housing MCC 1...-STZ-3,81 and MCC 1...-STZF-3,81, for cross sections of 0.2 mm<sup>2</sup> to 0.34 mm<sup>2</sup>

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1859988       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | AA02          |
| Product key                          | AABCAD        |
| GTIN                                 | 4017918109721 |
| Weight per piece (including packing) | 0.33 g        |
| Weight per piece (excluding packing) | 0.33 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# MCC-MT 0,2-0,35 - Crimp contact

1859988

<https://www.phoenixcontact.com/us/products/1859988>



## Technical data

### Product properties

|                |               |
|----------------|---------------|
| Product type   | Crimp contact |
| Product family | MCC-MT        |
| Pitch          | 0 mm          |


### Connection data

|                                         |                                              |
|-----------------------------------------|----------------------------------------------|
| Connection method                       | Crimp connection                             |
| Contact connection type                 | Socket                                       |
| Stripping length of the individual wire | 4 mm                                         |
| Stripping length                        | 4 mm ... 4.1 mm                              |
| Conductor cross-section flexible        | 0.2 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> |
| Conductor cross-section AWG             | 24 ... 22                                    |

### Material specifications

|                                        |         |
|----------------------------------------|---------|
| Contact surface                        | Tin Sn  |
| Contact surface material               | Tin     |
| Metal surface contact area (top layer) | Tin Sn) |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | -                                                                                    |

### Electrical properties

|                       |     |
|-----------------------|-----|
| Nominal current $I_N$ | 4 A |
|-----------------------|-----|

### Packaging specifications

|                   |            |
|-------------------|------------|
| Type of packaging | Bulk goods |
|-------------------|------------|

# MCC-MT 0,2-0,35 - Crimp contact





1859988

<https://www.phoenixcontact.com/us/products/1859988>



## Drawings

Dimensional drawing



# MCC-MT 0,2-0,35 - Crimp contact

1859988

<https://www.phoenixcontact.com/us/products/1859988>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460403 |
| ECLASS-15.0 | 27460403 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000796 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

# MCC-MT 0,2-0,35 - Crimp contact

1859988

<https://www.phoenixcontact.com/us/products/1859988>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)