

DFC T 2,4 QVGA S 7035 - Display



2203537

<https://www.phoenixcontact.com/us/products/2203537>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

TFT module 2.4", 320 x 240 pixels, transmissive, LED backlight, interface: SPI, operating temperature: -20°C ... 70°C; frame color (RAL): light gray (7035)



Your advantages

- Easy and time-saving integration into electronics housings of ME and ME-IO series
- Long-term availability
- Plastic frame available in different colors
- High-resolution
- Common interface for your electronics

Commercial data

Item number	2203537
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AC05
Product key	ACGAAB
GTIN	4055626960821
Weight per piece (including packing)	30.42 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85312040
Country of origin	DE

DFC T 2,4 QVGA S 7035 - Display

2203537

<https://www.phoenixcontact.com/us/products/2203537>



Technical data

Product properties

Product type	Display
Display	
Display type	Color display TFT
Display type	LCD with backlighting
Display type	transmissive
Panel technology	TFT
Diagonals (cm)	6.9 cm
Diagonals (inch)	2.4 in.
Screen resolution	320 x 240 Pixel(s) (QVGA)
Display formats	4:3
Display lighting type	LED, white
Contrast ratio	500
Viewing direction	6:00
Controller	HX8347I

Interfaces

Interface	SPI
-----------	-----

Dimensions

Dimensions	72 mm x 59 mm x 9 mm (Dimensions of the display frame)
	49 mm x 37 mm (Active range)

Material specifications

Color (Housing)	light gray (RAL 7035)
Surface characteristics	untreated

Environmental and real-life conditions

Vibration test	
Specification	IEC 60068-2-6:2007-12
Frequency	10 - 55 - 10 Hz
Sweep speed	1 octave/min
Test duration per axis	15 min
Test directions	X-, Y- and Z-axis

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-30 °C ... 80 °C

DFC T 2,4 QVGA S 7035 - Display



2203537

<https://www.phoenixcontact.com/us/products/2203537>

Classifications

ECLASS

ECLASS-15.0	27261890
ECLASS-13.0	27261890

ETIM

ETIM 9.0	EC011541
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

DFC T 2,4 QVGA S 7035 - Display



2203537

<https://www.phoenixcontact.com/us/products/2203537>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com