

SUP-10-SMA-5YR - Building management system



2404185

<https://www.phoenixcontact.com/us/products/2404185>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Maintenance license (5 years) for the SUP-10 Emalytics Supervisor license



Commercial data

Item number	2404185
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR18
Product key	DRHBAA
GTIN	4055626349350
Weight per piece (including packing)	0.001 MGM
Weight per piece (excluding packing)	0.001 MGM
Customs tariff number	49119900
Country of origin	US

SUP-10-SMA-5YR - Building management system



2404185

<https://www.phoenixcontact.com/us/products/2404185>

Technical data

Product properties

Product type	Building management system
Area of application	Building technology

System properties

Type of software	On-premises
Intended use for the software	Automation

License information

Type of license	Maintenance license
License duration	5 Years

Functionality

Integrated function	Analysis
	Data acquisition
	Diagnostics
	Startup
	Communication
	Configuration
	Project planning
	Simulation
Target system	Server
Supported controllers	ILC 2050 BI
Number of data points	not relevant
Number of clients	10

System requirements

Languages supported	German, English
Screen resolution	1024 x 768 pixel(s) ,or higher

SUP-10-SMA-5YR - Building management system



2404185

<https://www.phoenixcontact.com/us/products/2404185>

Classifications

ECLASS

ECLASS-13.0	27242590
ECLASS-15.0	27242590

ETIM

ETIM 9.0	EC001435
----------	----------

UNSPSC

UNSPSC 21.0	43233600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------