

FLKM-PA-D25/HW/AID16/C300 - Front adapter



2905198

<https://www.phoenixcontact.com/us/products/2905198>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Honeywell C300, series I/O, includes 16 differential signals (D1-D16) and 25-pos. D-SUB connector

Your advantages

- Preassembled system cables are connected directly to I/O modules using the front adapters
- Front adapter with D-SUB connector
- Connection of analog modules

Commercial data

Item number	2905198
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BMH
GTIN	4055626002989
Weight per piece (including packing)	78.2 g
Weight per piece (excluding packing)	74.2 g
Customs tariff number	85366990
Country of origin	US

Technical data

Product properties

Product type	Front adapter
Insulation characteristics	
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	< 50 V AC
	60 V DC
Max. permissible current	1 A (per path)
Supported controller HONEYWELL Experion PKS C300/C-Series	
Suitable I/O card	TAIX51 (non-redundant)
	TAID01 (non-redundant)

Connection data

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	25

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN EN 50178
	IEC 60664

Mounting


Mounting position	any
-------------------	-----

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings

Circuit diagram



FLKM-PA-D25/HW/AID16/C300 - Front adapter



2905198

<https://www.phoenixcontact.com/us/products/2905198>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905198>

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

FLKM-PA-D25/HW/AID16/C300 - Front adapter



2905198

<https://www.phoenixcontact.com/us/products/2905198>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 9.0	EC002584
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9e190ead-5376-43a8-a97b-5e96320b64dd