

UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination board, connection 1: Screw connection, connection 2: EDAC / ELCO pin strip 1x 56-position (ELCO pin strip type 8016/EDAC pin strip type 516, right)

Commercial data

Item number	2975900
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2186
GTIN	4017918089191
Weight per piece (including packing)	330.5 g
Weight per piece (excluding packing)	278.06 g
Customs tariff number	85366990
Country of origin	DE

UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	56

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	125 V AC/DC
Max. permissible current	1.5 A (per path)
Max. permissible total current	28 A (56 branches with 0.5 A each)

Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.5 kV

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	EDAC / ELCO pin strip
Coding	1-1
Number of connections	1
Number of positions	56
Note	ELCO pin strip type 8016/EDAC pin strip type 516, right

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	157.25 mm
-------	-----------

UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Height	77 mm
Depth	57.37 mm

Material specifications

Color	gray (RAL 7042)
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances	
Standards/regulations	EN 60664-1

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes

Notes on operation	Ensure that the supply voltage of the device has a common reference potential.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.


UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Drawings



UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Connection diagram

Terminal	Pin strip
Z	Z
1	A
2	B
3	C
4	D
5	E
6	F
7	H
8	J
9	K
10	L
11	M
12	N
13	P
14	R
15	S
16	T
17	U
18	V
19	W
20	X
21	a
22	b
23	c
24	d
25	e
26	f
27	h
28	j
29	k
30	l
31	m
32	n
33	p
34	r
35	s
36	t
37	u
38	v
39	w
40	x
41	y
42	z
43	AA
44	BB
45	CC
46	DD
47	EE
48	FF
49	HH
50	JJ
51	KK
52	LL
53	MM
54	NN
Y	Y (Shield)

UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2975900>



EAC

Approval ID: RU*DE.*09.B.00387/20

UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UMK- EC56/56-XOR - Termination board

2975900

<https://www.phoenixcontact.com/us/products/2975900>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com