

PR/2 - Latching

3040630

<https://www.phoenixcontact.com/us/products/3040630>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Latching, width: 10 mm, height: 29.8 mm, number of positions: 2, color: orange

Your advantages

- Can be used in all plug versions
- Snapped into the outside of the plug housing and hooks onto the terminal block housing when the plug is snapped on

Commercial data

Item number	3040630
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE02
Product key	BE214Z
GTIN	4017918832773
Weight per piece (including packing)	0.968 g
Weight per piece (excluding packing)	0.9 g
Customs tariff number	39269097
Country of origin	PL

PR/2 - Latching

3040630

<https://www.phoenixcontact.com/us/products/3040630>



Technical data

Product properties

Product type	Mounting material
Number of positions	2

Dimensions

Width	10 mm
Height	29.8 mm

Material specifications

Color	orange (RAL 2003)
Material	PA-GF
Flammability rating according to UL 94	HB

PR/2 - Latching

3040630

<https://www.phoenixcontact.com/us/products/3040630>



Classifications

ECLASS

ECLASS-15.0	27141192
ECLASS-13.0	27141192

ETIM

ETIM 9.0	EC004592
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PR/2 - Latching



3040630

<https://www.phoenixcontact.com/us/products/3040630>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com