

# STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/us/products/3190632>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module socket contact, inserted in the PCC or HCC plug housing after crimping the conductor, for 1.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup> conductors, ribbon contact

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3190632       |
| Packing unit                         | 3,300 pc      |
| Minimum order quantity               | 3,300 pc      |
| Sales key                            | AA03          |
| Product key                          | AACCEG        |
| GTIN                                 | 4017918100568 |
| Weight per piece (including packing) | 0.95 g        |
| Weight per piece (excluding packing) | 0.95 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | CN            |

# STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/us/products/3190632>

## Technical data

### Product properties

|                |           |
|----------------|-----------|
| Product type   | Connector |
| Product family | Metal     |
| Pitch          | 0 mm      |

### Electrical properties

|                       |      |
|-----------------------|------|
| Nominal current $I_N$ | 10 A |
|-----------------------|------|

### Dimensions

|       |   |
|-------|---|
| Pitch | - |
|-------|---|

### Material specifications

|                                        |         |
|----------------------------------------|---------|
| Contact surface                        | Tin Sn  |
| Contact surface material               | Tin     |
| Metal surface contact area (top layer) | Tin Sn) |

### Standards and regulations

|                                  |        |
|----------------------------------|--------|
| Connection in acc. with standard | EN-VDE |
|----------------------------------|--------|

# STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/us/products/3190632>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27469090 |
| ECLASS-15.0 | 27469090 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/us/products/3190632>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)