

ZB 13:UNBEDRUCKT - Zack marker strip



0829131

<https://www.phoenixcontact.com/us/products/0829131>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 13 mm, Number of individual labels: 5, text field height: 10.5 mm, text field width: 13 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

Commercial data

Item number	0829131
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
GTIN	4046356546430
Weight per piece (including packing)	1.648 g
Weight per piece (excluding packing)	1.411 g
Customs tariff number	39269097
Country of origin	DE

ZB 13:UNBEDRUCKT - Zack marker strip



0829131

<https://www.phoenixcontact.com/us/products/0829131>

Technical data

Notes

General	Can be labeled with CMS
General	Can be labeled with CMS

Product properties

Product type	Klemmenmarker
Pitch	13 mm

Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	5

Dimensions

Width	13.00 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	13 mm

Material specifications

Color	white (RAL 9010)
Material	PA
	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN EN 61010-1 (VDE 0411-1)
	DIN VDE 0611

ZB 13:UNBEDRUCKT - Zack marker strip



0829131

<https://www.phoenixcontact.com/us/products/0829131>

	DIN VDE 0611
--	--------------

Mounting

Mounting type	latching
---------------	----------

ZB 13:UNBEDRUCKT - Zack marker strip

0829131

<https://www.phoenixcontact.com/us/products/0829131>

Drawings

Schematic diagram



ZB 13:UNBEDRUCKT - Zack marker strip



0829131

<https://www.phoenixcontact.com/us/products/0829131>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 13:UNBEDRUCKT - Zack marker strip



0829131
<https://www.phoenixcontact.com/us/products/0829131>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.013 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com