

# BL2 BPC 1501E-W-128-W10-T - Box PC

1158231

<https://www.phoenixcontact.com/us/products/1158231>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Celeron® N3350 processor with 32 GB eMMC mass storage, 128 GB M.2 SSD, 2x COM ports, Windows 10 Enterprise 2019 LTSC operating system, Wi-Fi, and a Trusted Platform Module (TPM)

## Commercial data

Item number	1158231
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBABA
GTIN	4063151162498
Weight per piece (including packing)	920 g
Weight per piece (excluding packing)	650 g
Customs tariff number	84715000
Country of origin	TW

# BL2 BPC 1501E-W-128-W10-T - Box PC

1158231

<https://www.phoenixcontact.com/us/products/1158231>



## Technical data

### Notes

Note on application

Note on application

Only for industrial use

### Product properties

Product type	Box PC
Computer data	
Processor	Intel® Celeron® N3350 1.10/2.4 GHz
Operating system	Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language
RAM	4 GB LPDDR4
Data storage system	eMMC internal, 32 GB
	128 GB M.2 SSD
Cooling	passive

### Display

Display type	none
--------------	------

### System properties

User software	without user software
---------------	-----------------------

### Electrical properties

Maximum power dissipation for nominal condition	16.8 W
Supply	
Supply voltage (DC)	24 V DC ±20% (CE rating)
Supply voltage range	12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC)
Max. current consumption	0.7 A (24 V DC)
Typical current consumption	0.53 A (24 V DC)

### Connection data

#### Power supply

Connection method	Screw connection
Conductor cross-section, rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	7 mm

### Interfaces

Interfaces	1x DP++
	2x USB 3.0
	2x COM ports

# BL2 BPC 1501E-W-128-W10-T - Box PC

1158231

<https://www.phoenixcontact.com/us/products/1158231>



	1x Wireless LAN
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

## Dimensions

### External dimensions

Width / Height / Depth	99 mm / 92 mm / 63 mm
------------------------	-----------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-20 °C ... 50 °C (with 0.5 m/s airflow)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

## Approvals

### Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

## Mounting

Mounting type	DIN rail mounting
	Panel mounting (Accessories required)

# BL2 BPC 1501E-W-128-W10-T - Box PC

1158231

<https://www.phoenixcontact.com/us/products/1158231>



## Classifications

### ECLASS

ECLASS-13.0	19200102
-------------	----------

### ETIM

ETIM 9.0	EC001413
----------	----------

### UNSPSC

UNSPSC 21.0	43211500
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)