

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer for printing all materials in roll format with a print resolution of 300 dpi. Suitable for long-term use in production and for large print volumes, as large rolls can also be processed.

Product description

Benefit from the flexibility of the THERMOMARK E.300 industrial printer:

Use the printer to print all roll materials in the MARKING system portfolio for professional and durable wire and cable identification, equipment and plant identification, and terminal identification.

In addition to prepunched label formats, you can also process shrink sleeve as well as label material in continuous format. To do this, simply combine the printer with the THERMOMARK E.CUTTER or E.CUTTER/P for the convenient cutting or perforation of materials in continuous format.

For the maximum efficiency of identification processes, combine the standard printer with a THERMOMARK E SERIES applicator. This will transform your printer into an efficient printing and application system, enabling you to achieve an average time saving of 60% as the markers are printed and applied in just one automated process step. With the THERMOMARK E.300, the THERMOMARK E.WIRE and E.SLEEVE applicators can be used for efficient wire and cable identification and the THERMOMARK E.VARIO can be used for efficient terminal identification.

Scope of supply:

THERMOMARK E.300, power cable (pin connector pattern: type "B"), USB cable, EML (20X8)R/TL label roll (0802999), THERMOMARK-RIBBON 110/50 ink ribbon (0800687), multilingual packing slip

Your advantages

- Suitable for all roll materials in the MARKING system product portfolio
- The THERMOMARK E.300 can process larger material rolls than the THERMOMARK ROLL 2.0
- Continuous media in roll format can be easily cut or perforated using the THERMOMARK E.CUTTER (for cutting label material in continuous format) or the THERMOMARK E.CUTTER/P (for perforating shrink sleeve in continuous format)
- Easily transform the standard printer into an efficient printing and application system: Compatibility with the THERMOMARK E SERIES applicators THERMOMARK E.WIRE, E.SLEEVE, and E.VARIO
- When operating the printer with an applicator for wire and cable identification, convenient and intuitive project processing is possible directly via the 4.3" multicolor LCD touch display; the user also receives structured guidance and is supplied with the relevant information
- Easy handling of all status and error messages, as corresponding videos can be accessed and played directly via the touch display
- Status messages are conveniently sent in real time and bidirectionally to the marking software with OPC UA when operating the printer via the Ethernet interface
- The 300 dpi print resolution is the absolute industry standard for all conventional applications and materials
- Efficient and maintenance-free operation with proven thermal transfer printing technology
- Easy to control and manage with MARKING system software

Commercial data

Item number	1287021
Packing unit	1 pc

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
GTIN	4063151512163
Weight per piece (including packing)	12,800 g
Weight per piece (excluding packing)	9,780 g
Customs tariff number	84433210
Country of origin	DE

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

Technical data

Product properties

Product type	Marking system
Scope of supply	Ink ribbon, label roll, power cable, USB cable, operating instructions
	Power cable, USB cable, operating instructions, label roll, ink ribbon

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print width	105 mm
Print resolution	300 dpi
Operating system	Windows 10, Windows 11, Windows Server 2016, Windows Server 2019, Windows Server 2022

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	252 mm
Height	288 mm
Length	460 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
---------------------------------	----------------

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1287021>



cULus Listed

Approval ID: E140403



cULus Listed

Approval ID: E140403



IECEE CB Scheme

Approval ID: DK-112231-M2-UL

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

Classifications

ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

ETIM

ETIM 9.0	EC001684
----------	----------

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

Accessories

THERMOMARK E.WIRE - Applicator

1203216

<https://www.phoenixcontact.com/us/products/1203216>



Applicator for the efficient printing and application of movable E-WM... markers on wires and cables in a single automated process step

THERMOMARK E.SLEEVE - Applicator

1192932

<https://www.phoenixcontact.com/us/products/1192932>



Applicator for the efficient printing and application of E-WMS... shrink sleeves and marking sleeves on wires and cables in a single automated process step

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK E.CUTTER - Cutter

1234241

<https://www.phoenixcontact.com/us/products/1234241>

Cutter for marking materials in continuous format for cutting custom lengths



THERMOMARK E.CUTTER/P - Cutter

1201336

<https://www.phoenixcontact.com/us/products/1201336>

Perforation cutter for all shrink sleeve and marking sleeve versions in continuous format for cutting custom lengths



THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 110 - Ink ribbon

5145384

<https://www.phoenixcontact.com/us/products/5145384>



Ink ribbon, for roll printers for printing product groups TML..., TMT..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EMLC ..., EML-ESD..., EMLF ..., EML-HA ..., EML-LPR(D) ..., EML-LT ..., EMLP..., EML-RM..., EML-RS ..., EMLS..., EMT..., PML-GHS..., PML-T..., PML-P..., PML-W..., PMM..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110 BU - Ink ribbon

0829544

<https://www.phoenixcontact.com/us/products/0829544>



Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm, color: blue

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 110 GN - Ink ribbon

0829542

<https://www.phoenixcontact.com/us/products/0829542>

Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm, color: green



THERMOMARK-RIBBON 110 RD - Ink ribbon

0829543

<https://www.phoenixcontact.com/us/products/0829543>

Ink ribbon, length: 300 m, roll length: 300 m, width: 110 mm, color: red



THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 110/50 - Ink ribbon

0800687

<https://www.phoenixcontact.com/us/products/0800687>



Ink ribbon, for roll printers for printing product groups TML..., TMT..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EMLC ..., EML-ESD..., EMLF ..., EML-HA ..., EML-LPR(D) ..., EML-LT ..., EMLP..., EML-RM..., EML-RS ..., EMLS..., EMT..., PML-GHS..., PML-T..., PML-P..., PML-W..., PMM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

THERMOMARK-RIBBON 110-EML-HT - Ink ribbon

0800342

<https://www.phoenixcontact.com/us/products/0800342>



Ink ribbon, for roll printer for printing product group EML-HT..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 110-WMS - Ink ribbon

5145397

<https://www.phoenixcontact.com/us/products/5145397>



Ribbon sheet, length: 300 m, width: 110 mm, printing color: Black (specially for shrinking sleeves)

THERMOMARK-RIBBON 110-WMSU - Ink ribbon

0801358

<https://www.phoenixcontact.com/us/products/0801358>



Ink ribbon, For roll printer for printing product groups WMS..., WMS-2 HF..., and WMTB HF-HP, length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 110-WMSU WH - Ink ribbon

0801359

<https://www.phoenixcontact.com/us/products/0801359>



Ink ribbon, for roll printer for printing product group WMS... (black), length: 300 m, roll length: 300 m, width: 110 mm, color: white

THERMOMARK-RIBBON 110-WMTB HF - Ink ribbon

5148007

<https://www.phoenixcontact.com/us/products/5148007>



Ink ribbon, for roll printers for printing product groups WMTB HF..., WMS-2 HF..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 25-WMSU - Ink ribbon

0803390

<https://www.phoenixcontact.com/us/products/0803390>



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., length: 300 m, roll length: 300 m, width: 25 mm, color: black

THERMOMARK-RIBBON 64-WMSE - Ink ribbon

5145724

<https://www.phoenixcontact.com/us/products/5145724>



Ink ribbon, for roll printer for printing product group WMS..., length: 300 m, roll length: 300 m, width: 64 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 64-WMSE RD - Ink ribbon

5145740

<https://www.phoenixcontact.com/us/products/5145740>

Ink ribbon, length: 300 m, roll length: 300 m, width: 64 mm, color: red



THERMOMARK-RIBBON 64-WMSU - Ink ribbon

0801360

<https://www.phoenixcontact.com/us/products/0801360>

Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., length: 300 m, roll length: 300 m, width: 64 mm, color: black



THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-RIBBON 64-WMSU WH - Ink ribbon

0801361

<https://www.phoenixcontact.com/us/products/0801361>



Ink ribbon, for roll printer for printing product group WMS... (black), length: 300 m, roll length: 300 m, width: 64 mm, color: white

TM-RIBBON 105 BK 106 - Ink ribbon

1255597

<https://www.phoenixcontact.com/us/products/1255597>



Ink ribbon, for roll printer for printing product groups WMTB HF-D, length: 0.3 m, roll length: 300 m, width: 105 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TM-RIBBON 110 WH 100 - Ink ribbon

0804661

<https://www.phoenixcontact.com/us/products/0804661>



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing material-off-the-roll product groups: EML ..., EMLP ..., EMLF ..., PML-M . . ., WMTB HF-HP..., WMS-2 HF ... RD and US-material product groups: US-EML(S)P ..., US-EMLP-HA ..., US-EM(S)P ..., US-WMT ..., US-WMTB ..., US-PML-M ..., US-EMLF ..., roll length: 60 m, width: 110 mm, color: white

TM-RIBBON 110 WH 101 - Ink ribbon

1099966

<https://www.phoenixcontact.com/us/products/1099966>



Ink ribbon, For THERMOMARK roll printers for printing the product group material off the roll: PML-T..., roll length: 60 m, width: 110 mm, color: white

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TM-RIBBON 110-EX - Ink ribbon

0803211

<https://www.phoenixcontact.com/us/products/0803211>



Ink ribbon, for roll printer for printing product group EML-EX..., roll length: 280 m, width: 110 mm, color: black

TM-RIBBON 110-WMTB HF WH - Ink ribbon

0802990

<https://www.phoenixcontact.com/us/products/0802990>



Ink ribbon, for roll printer for printing product group WMTB HF..., length: 300 m, roll length: 300 m, width: 110 mm, color: white

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TM-RIBBON 25 BK 102 - Ink ribbon

1053499

<https://www.phoenixcontact.com/us/products/1053499>



Ink ribbon, for printing WMS-OT/WMS-2 HF... materials, length: 300 m, roll length: 300 m, width: 25 mm, color: black

TM-RIBBON 30 BK 103 - Ink ribbon

1309076

<https://www.phoenixcontact.com/us/products/1309076>



Ink ribbon, for the E-WM... product group in combination with the THERMOMARK E.WIRE applicator, length: 300 m, roll length: 300 m, width: 30 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TM-RIBBON 40 BK 105 - Ink ribbon

1259008

<https://www.phoenixcontact.com/us/products/1259008>



Ink ribbon, for the E-WMS... product group in combination with the THERMOMARK E.SLEEVE applicator and the WMS... and WMS-2 HF... product groups in combination with conventional roll printers, length: 300 m, roll length: 300 m, width: 40 mm, color: black

TM-RIBBON 64 BK 103 - Ink ribbon

1255598

<https://www.phoenixcontact.com/us/products/1255598>



Ink ribbon, For the E-WML... product group in combination with the THERMOMARK E.WRAP applicator, length: 300 m, roll length: 300 m, width: 64 mm, color: black

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TRM-PRESSURE ROLLER STANDARD - Pressure roller

0804655

<https://www.phoenixcontact.com/us/products/0804655>



Standard pressure roller

TRM-PRESSURE ROLLER 4-50 - Pressure roller

0804656

<https://www.phoenixcontact.com/us/products/0804656>



Pressure roller for continuous shrink sleeve

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TM E.WIRE/E.SLEEVE-PR - Pressure roller

1259203

<https://www.phoenixcontact.com/us/products/1259203>



Pressure roller for all E-WM... and E-WMS... materials (for material width of up to 30 mm/1.18")

TM E.300/E.600-TEAR OFF PLATE - Demolition plate

1263118

<https://www.phoenixcontact.com/us/products/1263118>



Tear-off plate for all roll printers in the THERMOMARK E SERIES

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

TM E.300/E.600-FRONT COVER - Front plate

1285305

<https://www.phoenixcontact.com/us/products/1285305>

Front panel for all roll printers in the THERMOMARK E SERIES



THERMOMARK ROLL-ERH - Media hub

5146448

<https://www.phoenixcontact.com/us/products/5146448>

External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm



THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK-ERH 500 - Media hub

5146309

<https://www.phoenixcontact.com/us/products/5146309>



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

THERMOMARK-CP - Accessories

5145371

<https://www.phoenixcontact.com/us/products/5145371>



Cleaning pen, for thermal transfer printers

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

CLEANING STICK - Cleaning pen

5146697

<https://www.phoenixcontact.com/us/products/5146697>



Cleaning stick for fast and efficient printhead cleaning of all Phoenix Contact thermal transfer printers.

TRM-MARGIN STOP - Locking

0804657

<https://www.phoenixcontact.com/us/products/0804657>



Locking

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

THERMOMARK ROLLMASTER-CASE - Case

0804643

<https://www.phoenixcontact.com/us/products/0804643>



Transport case for THERMOMARK ROLLMASTER and THERMOMARK E SERIES printers

MARKING SYSTEM SOFTWARE - Software

1669297

<https://www.phoenixcontact.com/us/products/1669297>



Create marking files easily and conveniently on your laptop or desktop PC. All Phoenix Contact marking systems as well as standard office printers can be controlled via the software. The software is available for download.

THERMOMARK E.300 US - Thermal transfer printer



1287021

<https://www.phoenixcontact.com/us/products/1287021>

PROJECT COMPLETE - Software

1050453

<https://www.phoenixcontact.com/us/products/1050453>



Intuitive planning and marking software for configuring terminal strips and for professional marking of marking materials for terminal blocks, conductors, cables, devices, and systems. The software is available for download

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com