

1422042  
<https://www.phoenixcontact.com/us/products/1422042>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, PUR halogen-free, yellow, 3-wire, color single wire: brown, blue, black, cable length: 100 m

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1422042                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF16                           |
| Product key                          | AF1IIA                         |
| GTIN                                 | 4055626325071                  |
| Weight per piece (including packing) | 22.22 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Customs tariff number                | 85444995                       |
| Country of origin                    | US                             |

# SAC-3P-0,25-OE-OE-240-100,0 US - Cable reel



1422042

<https://www.phoenixcontact.com/us/products/1422042>

## Technical data

### Product properties

|                     |                    |
|---------------------|--------------------|
| Product type        | Cable by the meter |
| Application         | Connector          |
| Number of positions | 3                  |


### Electrical properties

|                       |       |
|-----------------------|-------|
| Nominal voltage $U_N$ | 300 V |
|-----------------------|-------|

### Cable/line

|              |       |
|--------------|-------|
| Cable length | 100 m |
|--------------|-------|

#### PUR halogen-free yellow [240]

|                                 |                                                                                     |
|---------------------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Cable weight                    | 24 kg/km                                                                            |
| UL AWM Style                    | 20549                                                                               |
| Number of positions             | 3                                                                                   |
| Shielded                        | no                                                                                  |
| Cable type                      | PUR halogen-free yellow [240]                                                       |
| Conductor structure signal line | 32x 0.10 mm                                                                         |
| AWG signal line                 | 24                                                                                  |
| Conductor cross section         | 3x 0.25 mm <sup>2</sup> (Signal line)                                               |
| Wire diameter incl. insulation  | 1.17 mm ±0.02 mm                                                                    |
| External cable diameter         | 4.40 mm ±0.15 mm                                                                    |
| Outer sheath, material          | PUR                                                                                 |
| External sheath, color          | yellow                                                                              |
| Conductor material              | Bare Cu litz wires                                                                  |
| Material wire insulation        | PP                                                                                  |
| Single wire, color              | brown, blue, black                                                                  |
| Thickness, insulation           | ≥ 0.21 mm                                                                           |
| Thickness, outer sheath         | approx. 0.90 mm                                                                     |
| Overall twist                   | 3 wires, twisted                                                                    |
| Length of twist, overall twist  | 40 mm                                                                               |
| Max. conductor resistance       | 78 Ω/km (at 20 °C)                                                                  |
| Insulation resistance           | ≥ 1 GΩ*km (at 20 °C)                                                                |
| Nominal voltage, cable          | ≤ 300 V AC                                                                          |

# SAC-3P-0,25-OE-OE-240-100,0 US - Cable reel



1422042

<https://www.phoenixcontact.com/us/products/1422042>

|                                               |                                                                                                                                        |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Test voltage                                  | ≥ 3000 V AC (Spark test)                                                                                                               |
| Minimum bending radius, fixed installation    | 5 x D                                                                                                                                  |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                                 |
| Smallest bending radius, fixed installation   | 22 mm                                                                                                                                  |
| Smallest bending radius, movable installation | 44 mm                                                                                                                                  |
| Dynamic load capacity (bending)               | Max. bending cycles: 4000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815                                                                                               |
|                                               | in accordance with EN 50267-2-1                                                                                                        |
| Flame resistance                              | in accordance with UL 758/1581 FT2                                                                                                     |
| Resistance to oil                             | According to DIN EN 60811-2-1, 168 h at 100°C                                                                                          |
|                                               | according to UL 758, 168 h at 60 °C                                                                                                    |
| Other resistance                              | hydrolysis and microbe resistant                                                                                                       |
|                                               | Resistant to salt water                                                                                                                |
|                                               | abrasion-resistant                                                                                                                     |
|                                               | Low adhesion                                                                                                                           |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)                                                                                           |
|                                               | -25 °C ... 80 °C (Cable, flexible installation)                                                                                        |

# SAC-3P-0,25-OE-OE-240-100,0 US - Cable reel



1422042

<https://www.phoenixcontact.com/us/products/1422042>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27061801 |
| ECLASS-15.0 | 27061801 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC003249 |
|----------|----------|

# SAC-3P-0,25-OE-OE-240-100,0 US - Cable reel



1422042

<https://www.phoenixcontact.com/us/products/1422042>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)