


VS-ASI-FC-EPDM-BK 100M - Flat cable



1432415

<https://www.phoenixcontact.com/us/products/1432415>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface EPDM flat conductor in black, for additional power supply, 2 x 1.5 mm², 100 m ring

Commercial data

Item number	1432415
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LF A
GTIN	4046356349321
Weight per piece (including packing)	6,832 g
Weight per piece (excluding packing)	6,832 g
Customs tariff number	85444995
Country of origin	DE

VS-ASI-FC-EPDM-BK 100M - Flat cable



1432415

<https://www.phoenixcontact.com/us/products/1432415>

Technical data

Product properties

Product type	Data cable by the meter
Sensor type	AS-Interface
Number of positions	2

Interfaces

Signal type/category	AS-Interface
----------------------	--------------

Cable/line

Cable length	100 m
Cable weight	85 kg/km
Number of positions	2
Shielded	no
Conductor structure	2 x 1.5 mm ²
Conductor type	Flat cable
Conductor structure, voltage supply	76x 0.16 mm
AWG power supply	16
Conductor cross section	1.5 mm ²
Wire diameter incl. insulation	2.5 mm
Outer sheath, material	EPDM (rubber)
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	EPDM (rubber)
Single wire, color	brown, blue
Thickness, insulation	approx. 0.50 mm
Nominal voltage, cable	48 V (U ₀)
Test voltage	1000 V AC
Other resistance	Ozone and UV resistant
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation)
	-25 °C ... 85 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Flexibly installed)
	-40 °C ... 85 °C (fixed routing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

VS-ASI-FC-EPDM-BK 100M - Flat cable



1432415

<https://www.phoenixcontact.com/us/products/1432415>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-ASI-FC-EPDM-BK 100M - Flat cable



1432415

<https://www.phoenixcontact.com/us/products/1432415>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com