


VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface EPDM flat conductor in yellow, 2 x 1.5 mm², 1000 m on a disposable drum

Commercial data

Item number	1434646
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LF A
GTIN	4046356349277
Weight per piece (including packing)	60,000 g
Weight per piece (excluding packing)	60,000 g
Customs tariff number	85444995
Country of origin	DE

VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

Technical data

Product properties

Product type	Data cable by the meter
Sensor type	AS-Interface
Number of positions	2
Shielded	no

Interfaces

Signal type/category	AS-Interface
----------------------	--------------

Dimensions

Width	10 mm
Height	4 mm

Cable/line

Cable length	1000 m
Cable weight	85 kg/km
Number of positions	2
Shielded	no
Conductor structure	2 x 1.5 mm ²
Conductor type	Flat cable
Conductor structure signal line	76x 0.16 mm
AWG signal line	16
Conductor cross section	1.5 mm ²
Wire diameter incl. insulation	2.5 mm
Outer sheath, material	EPDM (rubber)
External sheath, color	lemon yellow RAL 1012
Conductor material	Tin-plated Cu litz wires
Material wire insulation	EPDM (rubber)
Single wire, color	brown, blue
Thickness, insulation	approx. 0.50 mm
Nominal voltage, cable	32 V (U ₀)
Test voltage	1000 V AC
Other resistance	Resistant to ozone
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation)
	-25 °C ... 85 °C (Cable, flexible installation)

FO cable

Transmission medium	Copper
---------------------	--------

Environmental and real-life conditions

Ambient conditions

VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

Ambient temperature (operation)	-25 °C ... 85 °C (Flexibly installed)
	-40 °C ... 85 °C (fixed routing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C

VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646

<https://www.phoenixcontact.com/us/products/1434646>

Classifications

UNSPSC

UNSPSC 21.0	26121707
-------------	----------

VS-ASI-FC-EPDM-YE 1000M - Flat cable



1434646
<https://www.phoenixcontact.com/us/products/1434646>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com