

SACC-AT04-3P-RS-IV - Connector housing



1520948

<https://www.phoenixcontact.com/us/products/1520948>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector housing, Crimp contacts

Commercial data

Item number	1520948
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF72
Product key	AF2IEA
GTIN	4063151985400
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	5.7 g
Country of origin	MX

SACC-AT04-3P-RS-IV - Connector housing



1520948

<https://www.phoenixcontact.com/us/products/1520948>

Technical data

Notes

General	AT04-3P-RD01BLK
General	Use with Size 16 pin contacts

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

Product properties

Product type	Contact insert
Series	AT04
Contact numbering	A, B, C
Shielded	no


Electrical properties

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
Insulation resistance	1000 MΩ (at 25 °C)
Nominal voltage U_N	50 V AC/DC (IEC rating)
Nominal current I_N	13 A (MAX)

Connection data

Connection method	Crimp contacts
-------------------	----------------

Dimensions

Dimensional drawing	
Width	21 mm
Height	24.4 mm
Length	43.2 mm

Material specifications

Seal material Profile gasket	Silicon
Seal material Cable seal	Silicon
Housing material	PA-GF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Characteristics

SACC-AT04-3P-RS-IV - Connector housing



1520948

<https://www.phoenixcontact.com/us/products/1520948>

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
------------------------------	--

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68 (in mated condition)
	IP69K (in mated condition)
Ambient temperature (operation)	-55 °C ... 125 °C

SACC-AT04-3P-RS-IV - Connector housing


1520948

<https://www.phoenixcontact.com/us/products/1520948>




Drawings

Dimensional drawing



AT04-3P top view and side view

Schematic diagram



AT04-3P pin assignment

SACC-AT04-3P-RS-IV - Connector housing



1520948

<https://www.phoenixcontact.com/us/products/1520948>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

SACC-AT04-3P-RS-IV - Connector housing



1520948

<https://www.phoenixcontact.com/us/products/1520948>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com