

VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 panel mounting frame, IP67, for push-pull interlocking, plastic, with the Freenet system, for square panel cutout, with grommet, without mounting screws

Commercial data

Item number	1608197
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNODB
GTIN	4046356159937
Weight per piece (including packing)	8.5 g
Weight per piece (excluding packing)	8.4 g
Customs tariff number	85389099
Country of origin	DE

VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame



1608197

<https://www.phoenixcontact.com/us/products/1608197>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 8.2 Connectors for Outside Environment (Balanced cabling) and chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	--

Product properties

Product type	Panel-mount frame
Application	Freenet
Type	Version 14
Number of positions	8
Connection profile	RJ45

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Transmission medium	Copper
---------------------	--------

Connection data

Connection technology	
Connection method	Spring-cage connection

Dimensions

Dimensional drawing	
Width	29.5 mm
Height	42 mm
Length	37 mm

Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR
Seal material, flat gasket	NBR
Housing material	Plastic
Housing surface material	PA, light gray

VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame

1608197

<https://www.phoenixcontact.com/us/products/1608197>



Contact surface material	Au/Ni
Contact carrier material	Polyester GF

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions


Ambient conditions	
Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Front mounting
---------------	----------------

Drawings

Dimensional drawing



Mounting cutout

VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame

1608197

<https://www.phoenixcontact.com/us/products/1608197>



Classifications

ECLASS

ECLASS-13.0	27440210
ECLASS-15.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-F1-RJ45-POBK-1R-F - Panel-mount frame

1608197

<https://www.phoenixcontact.com/us/products/1608197>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com