

VS-SCRJ-KS - Bend protection nut



1655056

<https://www.phoenixcontact.com/us/products/1655056>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bend protection sleeve, for SC-RJ/IP67 sleeve housing



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1655056 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Note | Made to order (non-returnable) |
| Product key | ABNNBZ |
| GTIN | 4046356011556 |
| Weight per piece (including packing) | 6.376 g |
| Weight per piece (excluding packing) | 5.716 g |
| Country of origin | DE |

VS-SCRJ-KS - Bend protection nut

1655056

<https://www.phoenixcontact.com/us/products/1655056>



Technical data

Product properties

| | |
|--------------------|------------------------|
| Product type | Bend protection sleeve |
| Type | SCRJ |
| Connection profile | SCRJ |
| Cable outlet | straight |

Electrical properties

| | |
|---------------------|----|
| Transmission medium | FO |
|---------------------|----|

Material specifications

| | |
|--|---------|
| Color | gray |
| Material | Plastic |
| Flammability rating according to UL 94 | V0 |
| Housing material | Plastic |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 5 mm ... 8.5 mm |
|-------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 80 °C |

VS-SCRJ-KS - Bend protection nut



1655056

<https://www.phoenixcontact.com/us/products/1655056>

Classifications

ETIM

ETIM 8.0

EC001679

UNSPSC

UNSPSC 21.0

39121400

VS-SCRJ-KS - Bend protection nut

1655056

<https://www.phoenixcontact.com/us/products/1655056>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|--|--|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com