

CK4,0-ED-2,50ST AG - Crimp contact



1663242

<https://www.phoenixcontact.com/us/products/1663242>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-03, Pin, turned, contact diameter: 4 mm, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14...14 , contact material: Cu alloy

Commercial data

Item number	1663242
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF65
Product key	AF7AIE
GTIN	4017918123055
Weight per piece (including packing)	3 g
Weight per piece (excluding packing)	3 g
Customs tariff number	85366990
Country of origin	DE

CK4,0-ED-2,50ST AG - Crimp contact



1663242

<https://www.phoenixcontact.com/us/products/1663242>

Technical data

Notes

General	for HC-M-02, HC-M-03, HC-M-03/04, HC-M-04, HC-Q02, HC-Q03, HC-Q04, and HC-COM-Q4/2 contact carriers
Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.

Product properties

Product type	Crimp contact
Series	HC-M-03
	HC-M-03/04
	HC-M-04
	HC-K
	HC-M-02
	HC-HS
	HC-COM
Contact material type	turned

Connection data


Connection technology	
Contact connection type	Pin
Connection method	Crimp connection

Conductor connection	
Stripping length	9 mm
Connection cross section	2.5 mm ² ... 2.5 mm ²
Connection cross section AWG	14 ... 14

Material specifications

Material Contact	Cu alloy
Material Contact surface	Ag

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	4 mm

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

CK4,0-ED-2,50ST AG - Crimp contact



1663242

<https://www.phoenixcontact.com/us/products/1663242>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK4,0-ED-2,50ST AG - Crimp contact




1663242

<https://www.phoenixcontact.com/us/products/1663242>

Drawings

Dimensional drawing



Dimensional drawing

CK4,0-ED-2,50ST AG - Crimp contact



1663242

<https://www.phoenixcontact.com/us/products/1663242>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1663242>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK4,0-ED-2,50ST AG - Crimp contact



1663242

<https://www.phoenixcontact.com/us/products/1663242>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK4,0-ED-2,50ST AG - Crimp contact



1663242

<https://www.phoenixcontact.com/us/products/1663242>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.025 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com