


FLKM 10/ZFKDS - Termination board



2302887

<https://www.phoenixcontact.com/us/products/2302887>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Standard 1:1 FLK module, with spring-cage connection and flat-ribbon cable connector, no. of positions 10

Commercial data

Item number	2302887
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2181
GTIN	4017918941406
Weight per piece (including packing)	69.3 g
Weight per piece (excluding packing)	66.3 g
Customs tariff number	85369010
Country of origin	DE

FLKM 10/ZFKDS - Termination board



2302887

<https://www.phoenixcontact.com/us/products/2302887>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	10

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 1 A

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μs)

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	10
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7 mm
Number of positions	10
Conductor cross-section rigid	0.2 mm² ... 4 mm²
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
	0.25 mm² ... 2.5 mm² (Ferrule without plastic sleeve)
	0.25 mm² ... 1.5 mm² (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 12
Pitch	5.08 mm

Signaling

Status display present	no
------------------------	----

Dimensions

FLKM 10/ZFKDS - Termination board



2302887

<https://www.phoenixcontact.com/us/products/2302887>

Item dimensions

Width	33.65 mm
Height	77 mm
Depth	52.34 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM 10/ZFKDS - Termination board


2302887

<https://www.phoenixcontact.com/us/products/2302887>



Drawings

Circuit diagram



FLKM 10/ZFKDS - Termination board



2302887

<https://www.phoenixcontact.com/us/products/2302887>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKM 10/ZFKDS - Termination board



2302887
<https://www.phoenixcontact.com/us/products/2302887>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com