

VIP-2/SC/PDM-2/12 SO - Potential distributors

2901797

<https://www.phoenixcontact.com/us/products/2901797>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module, with three equipotential busbars (UB1, UB2, UB3) for potential distribution, for mounting on NS 35 rails



Commercial data

Item number	2901797
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2B14
GTIN	4046356640572
Weight per piece (including packing)	143.2 g
Weight per piece (excluding packing)	143.2 g
Customs tariff number	85369010
Country of origin	US

Technical data

Notes

Type of insulation housing	Polyamide PA non-reinforced
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Product properties

Product type	Potential distributor
Product family	VARIOFACE Professional
Potential connections	Per potential (UB1, UB2, UB3) 3 power/4 distributor terminal blocks

Electrical properties

Nominal voltage U_N	30 V DC
Max. current carrying capacity per branch	6 A
Max. total current of all branches	18 A (per potential)

Input data

Potential connections	Per potential (UB1, UB2, UB3) 3 power/4 distributor terminal blocks
-----------------------	---

Connection data

Feed-in	
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	3
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 10

Distribution	
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of connections	12
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Material specifications

Color	gray (RAL 7042)
-------	-----------------

VIP-2/SC/PDM-2/12 SO - Potential distributors

2901797

<https://www.phoenixcontact.com/us/products/2901797>



Flammability rating according to UL 94 (Housing)

V0 (Housing)

Mounting

Mounting type

DIN rail mounting

Classifications

ECLASS

ECLASS-13.0	27400609
ECLASS-15.0	27400609

ETIM

ETIM 9.0	EC001894
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-2/SC/PDM-2/12 SO - Potential distributors

2901797

<https://www.phoenixcontact.com/us/products/2901797>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com