

EML (51X25)R SR CUS - Label



0824336

<https://www.phoenixcontact.com/us/products/0824336>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, can be ordered: by line, silver/matt, labeled according to customer specifications, mounting type: adhesive, text field height: 25 mm, text field width: 51 mm

Your advantages

- The EML ... self-adhesive device markers are particularly suitable for identification of various types of equipment in controller, system, and control cabinet building
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML ... materials are UL-listed
- A wide range of marker sizes and colors are available for custom designs
- Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements

Commercial data

Item number	0824336
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4046356352017
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Width	51.00 mm
Height	25.00 mm
Depth	0.08 mm
Length	25 mm

Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive strength	24 µm
Adhesive	Acrylic
Color	silver/matt
Material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 5 °C
Recommended storage conditions	23 °C / 50 % relative humidity
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

EML (51X25)R SR CUS - Label



0824336

<https://www.phoenixcontact.com/us/products/0824336>

Mounting type	adhesive
---------------	----------

EML (51X25)R SR CUS - Label

0824336

<https://www.phoenixcontact.com/us/products/0824336>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0824336>



cULus Recognized

Approval ID: MH48542

EML (51X25)R SR CUS - Label



0824336

<https://www.phoenixcontact.com/us/products/0824336>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EML (51X25)R SR CUS - Label



0824336

<https://www.phoenixcontact.com/us/products/0824336>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com