

# EML (70X50)R SR CUS - Label



0824344

<https://www.phoenixcontact.com/us/products/0824344>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, can be ordered: by line, silver/matt, labeled according to customer specifications, mounting type: adhesive, text field height: 50 mm, text field width: 70 mm

## Your advantages

- The EML ... self-adhesive device markers are particularly suitable for identification of various types of equipment in controller, system, and control cabinet building
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML ... materials are UL-listed
- A wide range of marker sizes and colors are available for custom designs
- Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0824344                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8141                         |
| GTIN                                 | 4046356352086                  |
| Weight per piece (including packing) | 1.99 g                         |
| Weight per piece (excluding packing) | 1.99 g                         |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | Gerätemarker |
|--------------|--------------|

### Marking

|                                     |                |
|-------------------------------------|----------------|
| Number of individual labels per row | 1              |
| Identification technology           | Thermotransfer |

### Dimensions

|        |          |
|--------|----------|
| Width  | 70.00 mm |
| Height | 50.00 mm |
| Depth  | 0.08 mm  |
| Length | 50 mm    |

### Material specifications

|                   |                                |
|-------------------|--------------------------------|
| RoHS compliant    | yes                            |
| Foil strength     | 50 µm                          |
| Adhesive strength | 24 µm                          |
| Adhesive          | Acrylic                        |
| Color             | silver/matt                    |
| Material          | Polyester                      |
| Components        | free from silicone and halogen |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Ambient conditions

|                                                     |                                |
|-----------------------------------------------------|--------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 150 °C              |
| Ambient temperature (assembly)                      | > 5 °C                         |
| Recommended storage conditions                      | 23 °C / 50 % relative humidity |
| Recommended ambient temperature (storage/transport) | 22 °C                          |
| Recommended humidity (storage/transport)            | 50 %                           |
| Shelf life                                          | 2 years                        |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

# EML (70X50)R SR CUS - Label



0824344

<https://www.phoenixcontact.com/us/products/0824344>

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# EML (70X50)R SR CUS - Label

0824344

<https://www.phoenixcontact.com/us/products/0824344>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0824344>



**cULus Recognized**  
Approval ID: MH48542

# EML (70X50)R SR CUS - Label



0824344

<https://www.phoenixcontact.com/us/products/0824344>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# EML (70X50)R SR CUS - Label



0824344  
<https://www.phoenixcontact.com/us/products/0824344>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)