

UC-PMLP (90X38) CUS - Plastic label

0831039

<https://www.phoenixcontact.com/us/products/0831039>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Sheet, white, labeled, mounting type: adhesive, text field height: 90 mm, text field width: 38 mm



Your advantages

- The UC-PMLP ... plant identification family includes self-adhesive plant markers with excellent adhesive strength
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0831039
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Product key	BG8157
GTIN	4046356940702
Weight per piece (including packing)	99.99 g
Weight per piece (excluding packing)	9.8 g
Country of origin	PL

UC-PMLP (90X38) CUS - Plastic label

0831039

<https://www.phoenixcontact.com/us/products/0831039>



Technical data

Product properties

Product type	Plant marker
Marking	
Identification technology	UV LED technology

Dimensions

Width	90.00 mm
Height	38.00 mm
Depth	1.15 mm
Length	38 mm

Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	white
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

UC-PMLP (90X38) CUS - Plastic label

0831039

<https://www.phoenixcontact.com/us/products/0831039>



Standards

Standards/regulations

EN 45545-2

Mounting

Mounting type

adhesive

UC-PMLP (90X38) CUS - Plastic label

0831039

<https://www.phoenixcontact.com/us/products/0831039>



Classifications

ECLASS

ECLASS-13.0	27281104
ECLASS-15.0	27281104

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-PMLP (90X38) CUS - Plastic label

0831039

<https://www.phoenixcontact.com/us/products/0831039>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.136 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com