

PMM (EX40)R YE - Magnetic label



1014314

<https://www.phoenixcontact.com/us/products/1014314>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Magnetic label, Roll, yellow, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: magnetic adhesion, Number of individual labels: 1, roll length: 15 m, text field height: 40 mm, text field width: 15000 mm

Your advantages

- The magnetic labels supplied in rolls represent an individual and flexible marking solution, e.g., for warehouse marking
- High adhesive strength
- The flexible magnetic tape will also adhere to round objects with a radius from 12 mm
- Magnetic tape coated with polyester foil
- Magnetic labels, unprinted

Commercial data

Item number	1014314
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG21
Product key	BG2611
GTIN	4046356786188
Weight per piece (including packing)	1,216.9 g
Weight per piece (excluding packing)	1,216.9 g
Customs tariff number	39207380
Country of origin	DE

PMM (EX40)R YE - Magnetic label



1014314

<https://www.phoenixcontact.com/us/products/1014314>

Technical data

Product properties

Product type	Plant marker
Area of application	Magnetic labels
	Warehousing/logistics
Product property	magnetic

Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Length of roll	15.00 m
Height	40.00 mm
Depth	0.60 mm

Material specifications

Color	yellow (RAL 1018)
Material	Magnetic tape
Coating	Polyester foil

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Ambient conditions

Ambient temperature (operation)	-30 °C ... 55 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

PMM (EX40)R YE - Magnetic label



1014314

<https://www.phoenixcontact.com/us/products/1014314>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	magnetic adhesion
---------------	-------------------

PMM (EX40)R YE - Magnetic label



1014314

<https://www.phoenixcontact.com/us/products/1014314>

Classifications

ECLASS

ECLASS-13.0	27281104
ECLASS-15.0	27281104

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

PMM (EX40)R YE - Magnetic label



1014314
<https://www.phoenixcontact.com/us/products/1014314>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com