

ME MAX 45 PLATE U42 BK - Insertion plate



1029069

<https://www.phoenixcontact.com/us/products/1029069>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Insertion plate, width: 41.8 mm, height: 42 mm, depth: 1 mm, color: black (similar RAL 9005)

Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	1029069
Packing unit	10 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4055626530314
Weight per piece (including packing)	2.18 g
Weight per piece (excluding packing)	1.9 g
Country of origin	DE

ME MAX 45 PLATE U42 BK - Insertion plate

1029069

<https://www.phoenixcontact.com/us/products/1029069>



Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Product family	ME MAX 45..
Ventilation openings present	no

Dimensions

Width	41.8 mm
Height	42 mm
Depth	1 mm

Material specifications

Color (Insertion plate)	black (RAL 9005)
Material Housing	PA
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

ME MAX 45 PLATE U42 BK - Insertion plate

1029069

<https://www.phoenixcontact.com/us/products/1029069>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1029069>



UL Recognized

Approval ID: E240868

ME MAX 45 PLATE U42 BK - Insertion plate

1029069

<https://www.phoenixcontact.com/us/products/1029069>



Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

ME MAX 45 PLATE U42 BK - Insertion plate



1029069

<https://www.phoenixcontact.com/us/products/1029069>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com