

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

ECOR-2 relay base, for industrial relay with 2 or 4 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Commercial data

Item number	1089994
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C463
Product key	DKF312
GTIN	4055626897837
Weight per piece (including packing)	68.75 g
Weight per piece (excluding packing)	68 g
Customs tariff number	85366990
Country of origin	CN

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



Technical data

Notes

Notes on operation	Do not use to separate SELV / PELV circuits from other circuits, because safe isolation is not guaranteed.
Notes on operation	The outputs are not suitable for switching different outer conductors.
Notes on operation	The system installer must ensure the touch protection of the product (at voltages > 25 V AC/60 V DC). The product is a built-in device without protection against direct contact.
Notes on operation	At least a basic level of insulation is maintained against adjacent modules in the DIN rail direction. If the application has higher requirements on the insulation (reinforced insulation), then these must be realized through suitable measures (e.g. partition plates).

Product properties

Product type	Relay socket
Product family	ESSENTIAL edition
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	≤ 230 V AC/DC
Test voltage relay winding/relay contact	2.5 kV _{rms} (50 Hz, 1 min.)

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V AC
Rated surge voltage	2.5 kV

Connection data

Input side

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² (without ferrule) 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section AWG	12
Tightening torque	0.5 Nm ... 0.7 Nm

Output side

Connection method	Screw connection
Stripping length	7 mm

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² (without ferrule) 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section AWG	12
Tightening torque	0.5 Nm ... 0.7 Nm

Dimensions

Width	27 mm
Height	75 mm
Depth Retaining bracket	84 mm (with retaining bracket)

Material specifications

Color	traffic grey B (RAL 7043)
-------	---------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 ()
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1089994>



cUL Recognized

Approval ID: FILE E 113228



UL Recognized

Approval ID: FILE E 113228



cULus Recognized

Approval ID: E113228

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 9.0	EC001456
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

Mandatory accessories

REL-IR-BL/L- 12DC/4X21 - Single relay

1109557

<https://www.phoenixcontact.com/us/products/1109557>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 12 V DC

REL-IR-BL/L- 48DC/4X21 - Single relay

1109558

<https://www.phoenixcontact.com/us/products/1109558>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 48 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L-110DC/4X21 - Single relay

1109560

<https://www.phoenixcontact.com/us/products/1109560>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 110 V DC

REL-IR-BL/L-125DC/4X21 - Single relay

1109561

<https://www.phoenixcontact.com/us/products/1109561>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 125 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L-220DC/4X21 - Single relay

1109562

<https://www.phoenixcontact.com/us/products/1109562>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 220 V DC

REL-IR-BL/L- 24AC/4X21 - Single relay

1109563

<https://www.phoenixcontact.com/us/products/1109563>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 24 V AC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L-115AC/4X21 - Single relay

1109564

<https://www.phoenixcontact.com/us/products/1109564>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 115 V AC

REL-IR-BL- 24DC/4X21 - Single relay

1032521

<https://www.phoenixcontact.com/us/products/1032521>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test key, mechanical switch position indicator, polarity A1+, A2-, input voltage: 24 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL-230AC/4X21 - Single relay

1032529

<https://www.phoenixcontact.com/us/products/1032529>



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test key, mechanical switch position indicator, input voltage: 230 V AC

REL-IR-BL/L-230AC/4X21 - Single relay

1032531

<https://www.phoenixcontact.com/us/products/1032531>



Plug-in industrial relay with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 230 V AC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L- 24DC/4X21 - Single relay

1032527

<https://www.phoenixcontact.com/us/products/1032527>



Plug-in industrial relay with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 24 V DC

REL-IR-BL/L- 24DC/2X21 - Single relay

1032526

<https://www.phoenixcontact.com/us/products/1032526>



Plug-in industrial relay with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 24 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL- 24DC/2X21 - Single relay

1032470

<https://www.phoenixcontact.com/us/products/1032470>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test key, mechanical switch position indicator, polarity A1+, A2-, input voltage: 24 V DC

REL-IR-BL/L-230AC/2X21 - Single relay

1032530

<https://www.phoenixcontact.com/us/products/1032530>



Plug-in industrial relay with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 230 V AC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL-230AC/2X21 - Single relay

1032528

<https://www.phoenixcontact.com/us/products/1032528>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test key, mechanical switch position indicator, input voltage: 230 V AC

REL-IR-BL/L- 12DC/2X21 - Single relay

1109547

<https://www.phoenixcontact.com/us/products/1109547>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 12 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L- 48DC/2X21 - Single relay

1109548

<https://www.phoenixcontact.com/us/products/1109548>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 48 V DC

REL-IR-BL/L-110DC/2X21 - Single relay

1109550

<https://www.phoenixcontact.com/us/products/1109550>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 110 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L-125DC/2X21 - Single relay

1109553

<https://www.phoenixcontact.com/us/products/1109553>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 125 V DC

REL-IR-BL/L-220DC/2X21 - Single relay

1109554

<https://www.phoenixcontact.com/us/products/1109554>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, polarity A1+, A2-, input voltage: 220 V DC

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

REL-IR-BL/L- 24AC/2X21 - Single relay

1109555

<https://www.phoenixcontact.com/us/products/1109555>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 24 V AC

REL-IR-BL/L-115AC/2X21 - Single relay

1109556

<https://www.phoenixcontact.com/us/products/1109556>



Plug-in industrial relay in basic design with power contacts, 2 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 115 V AC

Accessories

ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



DB 50- 90 BU - Wire bridge

2821180

<https://www.phoenixcontact.com/us/products/2821180>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: blue



DB 50- 90 BK - Wire bridge

2820916

<https://www.phoenixcontact.com/us/products/2820916>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: black



ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

DB 50- 90 GY - Wire bridge

2820929

<https://www.phoenixcontact.com/us/products/2820929>

Flexible wire loop bridge, 50-pos., conductor cross-section: 0.5 mm², loop length: 90 mm, ferrule length: 8 mm, color: gray



LDP- 12- 24DC - Plug-in module

2833657

<https://www.phoenixcontact.com/us/products/2833657>

Plug-in module, with freewheeling diode and yellow LED, polarity: A1+, A2-, input voltage: 12 ... 24 V DC ±20 %



ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

DP-12-220 DC - Plug-in module

2907517

<https://www.phoenixcontact.com/us/products/2907517>



Plug-in module, with freewheeling diode, polarity: A1+, A2-, input voltage: 12 V DC ... 220 V DC $\pm 20\%$

LV-120-230AC/110DC - Plug-in module

2833738

<https://www.phoenixcontact.com/us/products/2833738>



Plug-in module, with varistor and yellow LED, input voltage: 120 ... 230 V AC / 110 V DC $\pm 20\%$

ECOR-2-BSC2/4X21 - Relay base



1089994

<https://www.phoenixcontact.com/us/products/1089994>

V-120-230UC - Plug-in module

2833880

<https://www.phoenixcontact.com/us/products/2833880>

Plug-in module, with varistor, input voltage: 120 ... 230 V AC/DC $\pm 20\%$



RC-120-230UC - Plug-in module

2833767

<https://www.phoenixcontact.com/us/products/2833767>

Plug-in module, with RC element, input voltage: 120 ... 230 V AC/DC $\pm 20\%$



ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/us/products/1089994>



MP 2 - Marker labels

2833644

<https://www.phoenixcontact.com/us/products/2833644>

Equipment marker, labeling surface 9 x 25 mm



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com