

SHN 13 - Tool

1209923

<https://www.phoenixcontact.com/us/products/1209923>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Socket wrench, wrench size 13 mm

Your advantages

- Ergonomically designed two-component handles for fatigue-proof and non-slip use

Commercial data

Item number	1209923
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH314C
GTIN	4046356178730
Weight per piece (including packing)	123.79 g
Weight per piece (excluding packing)	123.79 g
Customs tariff number	82054000
Country of origin	CZ

SHN 13 - Tool

1209923

<https://www.phoenixcontact.com/us/products/1209923>



Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Socket wrench
Type	Hexagonal

Connection data

Output	External hexagonal
--------	--------------------

Dimensions

Width	40 mm
Blade height	80 mm
Length	199 mm
Diameter	40 mm
Wrench size	13 mm
Wrench size for mounting	13 mm

Material specifications

Color	multicolored (RAL -)
Material	alloyed tool steel

SHN 13 - Tool

1209923

<https://www.phoenixcontact.com/us/products/1209923>



Classifications

ECLASS

ECLASS-13.0	21040206
ECLASS-15.0	21040206

ETIM

ETIM 9.0	EC000174
----------	----------

UNSPSC

UNSPSC 21.0	27111700
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com