

BL2 BPC 1501E-W-128 - Box PC

1305860

<https://www.phoenixcontact.com/us/products/1305860>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Celeron® N3350 processor with 32 GB eMMC mass storage, 128 GB M.2 SSD, 2x COM ports and Wi-Fi



Commercial data

Item number	1305860
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	NULL
Product key	DRBABA
GTIN	4063151552572
Weight per piece (including packing)	935.2 g
Weight per piece (excluding packing)	935.2 g
Customs tariff number	84715000
Country of origin	TW

BL2 BPC 1501E-W-128 - Box PC

1305860

<https://www.phoenixcontact.com/us/products/1305860>



Technical data

Product properties

Product type	Box PC
Computer data	
Processor	Intel® Celeron® N3350 1.10/2.4 GHz
Operating system	without operating system
RAM	4 GB LPDDR4
Data storage system	eMMC internal, 32 GB 128 GB M.2 SSD
Cooling	passive
Display	
Display type	none

Electrical properties

Supply	
Supply voltage	24 V DC ±20% (CE rating)
Supply voltage range	12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC)
Max. current consumption	0.7 A (24 V DC)
Typical current consumption	0.53 A (24 V DC)

Connection data

Power supply	
Connection method	Screw connection
Conductor cross-section, rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	7 mm

Interfaces

Interfaces	1x DP++ 2x USB 3.0 2x COM ports 1x Wireless LAN
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions	
Width / Height / Depth	99 mm / 92 mm / 63 mm

BL2 BPC 1501E-W-128 - Box PC

1305860

<https://www.phoenixcontact.com/us/products/1305860>



Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
	IP30
Ambient temperature (operation)	-20 °C ... 50 °C (with 0.5 m/s airflow)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

BL2 BPC 1501E-W-128 - Box PC

1305860

<https://www.phoenixcontact.com/us/products/1305860>



Classifications

ETIM

ETIM 8.0

EC001413

UNSPSC

UNSPSC 21.0

43211500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com