

# SAC-3P-22AWG-OE-OE-544-100,0SH - Cable reel



1318404

<https://www.phoenixcontact.com/us/products/1318404>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, shielded, PVC, gray, 3-wire, color single wire: brown, blue, black, cable length: 100 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1318404       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF16          |
| Product key                          | AF1IIB        |
| GTIN                                 | 4063151601706 |
| Weight per piece (including packing) | 22.22 g       |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85444995      |
| Country of origin                    | US            |

# SAC-3P-22AWG-OE-OE-544-100,0SH - Cable reel



1318404

<https://www.phoenixcontact.com/us/products/1318404>

## Technical data


### Product properties

|                     |                    |
|---------------------|--------------------|
| Product type        | Cable by the meter |
| Application         | Connector          |
| Number of positions | 3                  |

### Cable/line

|              |       |
|--------------|-------|
| Cable length | 100 m |
|--------------|-------|

PVC gray 105 °C [544]

|                                               |                                                                                     |
|-----------------------------------------------|-------------------------------------------------------------------------------------|
| Dimensional drawing                           |  |
| Cable weight                                  | 40 kg/km                                                                            |
| UL AWM Style                                  | 2517 (105 °C / 300 V)                                                               |
| Number of positions                           | 3                                                                                   |
| Shielded                                      | yes                                                                                 |
| Cable type                                    | PVC gray 105 °C [544]                                                               |
| Conductor structure signal line               | 7x 0.25 mm                                                                          |
| AWG signal line                               | 22                                                                                  |
| Wire diameter incl. insulation                | 1.27 mm ±0.03 mm                                                                    |
| External cable diameter                       | 5.20 mm ±0.2 mm                                                                     |
| Outer sheath, material                        | PVC                                                                                 |
| External sheath, color                        | gray                                                                                |
| Conductor material                            | Tin-plated Cu litz wires                                                            |
| Material wire insulation                      | PVC                                                                                 |
| Single wire, color                            | brown, blue, black                                                                  |
| Overall twist                                 | 3 wires, twisted                                                                    |
| Optical shield covering                       | 85 %                                                                                |
| Max. conductor resistance                     | max. 50.5 Ω/km (20 °C)                                                              |
| Insulation resistance                         | ≥ (550 M Ohms/m @ 500V)                                                             |
| Nominal voltage, cable                        | 300 V                                                                               |
| Minimum bending radius, flexible installation | 12 x D                                                                              |
| Smallest bending radius, movable installation | 63 mm                                                                               |
| Flame resistance                              | FT4                                                                                 |
| Other resistance                              | UV resistant                                                                        |
| Special properties                            | UL standards PLTC and ITC                                                           |

# SAC-3P-22AWG-OE-OE-544-100,0SH - Cable reel



1318404

<https://www.phoenixcontact.com/us/products/1318404>

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Ambient temperature (operation) | -30 °C ... 105 °C (cable, fixed installation)   |
|                                 | -5 °C ... 105 °C (Cable, flexible installation) |

# SAC-3P-22AWG-OE-OE-544-100,0SH - Cable reel



1318404

<https://www.phoenixcontact.com/us/products/1318404>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27061801 |
| ECLASS-15.0 | 27061801 |

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC003249 |
|----------|----------|

# SAC-3P-22AWG-OE-OE-544-100,0SH - Cable reel



1318404

<https://www.phoenixcontact.com/us/products/1318404>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)