

SACC-FP-M-M12-9 THR PP - Housing screw connection



1341713

<https://www.phoenixcontact.com/us/products/1341713>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Your advantages

- Manufacturer-independent M12 push-pull locking system for maximum availability
- Easy and quick cabling of devices and systems in hard-to-reach areas
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Flexible PCB assembly: two-piece connectors for wave and THR soldering

Commercial data

Item number	1341713
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQAAB
GTIN	4063151650551
Weight per piece (including packing)	9.618 g
Weight per piece (excluding packing)	8.296 g
Customs tariff number	74198090
Country of origin	DE

SACC-FP-M-M12-9 THR PP - Housing screw connection



1341713

<https://www.phoenixcontact.com/us/products/1341713>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	If necessary, order locking nut separately

Product properties

Product type	Circular connector housing
Thread type	M12

Connection data

Connection method	THR and wave soldering
Tightening torque	2 ... 3 Nm

Material specifications

Material	Brass, nickel-plated
Flammability rating according to UL 94	V0
Seal material	EPDM
Material for screw connection	Brass, nickel-plated

Connector

Connection 1

Head design	Pin
Head thread type	M12
Head locking type	Push-pull external locking

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

Environmental and real-life conditions

Ambient conditions	
Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP65/IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

SACC-FP-M-M12-9 THR PP - Housing screw connection



1341713

<https://www.phoenixcontact.com/us/products/1341713>

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	based on IEC 61076-2-010
Note	Push-pull

Mounting

Mounting type	Front mounting
---------------	----------------

SACC-FP-M-M12-9 THR PP - Housing screw connection



1341713

<https://www.phoenixcontact.com/us/products/1341713>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 9.0	EC003556
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-FP-M-M12-9 THR PP - Housing screw connection



1341713

<https://www.phoenixcontact.com/us/products/1341713>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com