

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting

Commercial data

Item number	1419001
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAE
GTIN	4046356521567
Weight per piece (including packing)	12.3 g
Weight per piece (excluding packing)	10.034 g
Customs tariff number	85366990
Country of origin	PL

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
No. of cable outlets	1
Shielded	yes
Cable outlet	straight
Positions/contacts	8P8C

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Contact resistance	< 20 mΩ (Contact)
	< 100 mΩ (shield)
Frequency range	to 500 MHz
Insulation resistance	> 500 MΩ
Nominal voltage U_N	48 V
Nominal current I_N	1.75 A
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 mΩ (Wire – IDC)
	0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	10 Gbps
Transmission characteristics (category)	CAT6 _A
Transmission speed	10 Gbps
Wave impedance	100 Ω

Connection data

Connection technology

Connection method	Insulation displacement connection
Connection cross section AWG	26 ... 24 (solid)
	26 ... 24 (flexible)
Conductor cross section	0.14 mm ² ... 0.22 mm ² (solid)
	0.14 mm ² ... 0.22 mm ² (flexible)
Connection in acc. with standard	IEC 60603-7-51
Cable outlet, angle	180

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Dimensions

Width	13.8 mm
Height	17.3 mm
Length	55.5 mm

Material specifications

Color	black
Flammability rating according to UL 94	V2
Housing material	Plastic
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
Locking latch material	PC
Material for screw connection	PA

Cable/line

External cable diameter	4.5 mm ... 8 mm
External cable diameter	4.5 mm ... 8 mm
Cable cross section	0.14 mm ²
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V
Wave impedance	100 Ω

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Test specification

Type of test	Vibration test
Specification	IEC 60068-2-6
Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Mounting

Mounting type	For field assembly
---------------	--------------------

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1419001>

 UL Listed Approval ID: E335024-20150529				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	57 V	1.75 A	-	-

 cUL Listed Approval ID: E335024-20150529				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	57 V	1.75 A	-	-

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Classifications

ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

ETIM

ETIM 9.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-08-RJ45-10G/Q - RJ45 connector



1419001

<https://www.phoenixcontact.com/us/products/1419001>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com