

CUC-DST-ABK-CP9 - Bend protection sleeve



1419792

<https://www.phoenixcontact.com/us/products/1419792>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bend protection sleeve, degree of protection: IP20, color: black

Commercial data

Item number	1419792
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	ABNCBZ
GTIN	4055626188218
Weight per piece (including packing)	1.52 g
Weight per piece (excluding packing)	1.44 g
Country of origin	DE

CUC-DST-ABK-CP9 - Bend protection sleeve



1419792

<https://www.phoenixcontact.com/us/products/1419792>

Technical data

Product properties

Product type	Sleeve housings
--------------	-----------------

Dimensions

Width	14.9 mm
Height	12.4 mm
Depth	17.2 mm
Length	28 mm

Material specifications

Color	black
Seal material	Thermoplastic elastomers

Cable/line

External cable diameter	7 mm ... 9 mm
-------------------------	---------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-35 °C ... 100 °C

CUC-DST-ABK-CP9 - Bend protection sleeve



1419792

<https://www.phoenixcontact.com/us/products/1419792>

Classifications

ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-DST-ABK-CP9 - Bend protection sleeve



1419792
<https://www.phoenixcontact.com/us/products/1419792>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com