

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marshalling panel, design: RJ45, degree of protection: IP20, material: PC-GF, connection method: Quick connection, housing size: 1, color: black



## Your advantages

- Assembly without special tools
- Rugged design

## Commercial data

Item number	1422979
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNLBA
GTIN	4055626319933
Weight per piece (including packing)	810 g
Weight per piece (excluding packing)	810 g
Customs tariff number	85389099
Country of origin	CN

## Technical data

### Product properties

Product type	Patch panel
Application	Installation slots for RJ45 cable connection module, adapter-free, and various FO couplings
Connection profile	RJ45
No. of cable outlets	24
Number of slots	24

### Electrical properties

Insulation resistance	according to IEC 61010-1
Transmission medium	FO

### Connection data

Connection method	Quick connection
-------------------	------------------

### Dimensions

Width	482.6 mm
Height	43.6 mm
Depth	83.4 mm

### Material specifications

Color	black
Material	Steel, galvanized
Flammability rating according to UL 94	V0
Housing material	PC-GF
Standards/regulations	Steel, galvanized

### Cable/line

Tensile strength short-term/long-term	150N (Modul)
---------------------------------------	--------------

### Mechanical properties

Tensile strength short-term/long-term	150N (Modul)
---------------------------------------	--------------

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	5 °C ... 55 °C
Ambient temperature (storage/transport)	-5 °C ... 55 °C
Ambient temperature (assembly)	-25 °C ... 55 °C

### Mounting

# CUC-PP-FR19:1U-I-EMPTY:24 BK - Marshalling panel

1422979

<https://www.phoenixcontact.com/us/products/1422979>



Mounting type	19" rack
Assembly note	Observe the grounding concept

## Classifications

### ECLASS

ECLASS-13.0	19170192
ECLASS-15.0	19170192

### ETIM

ETIM 9.0	EC003626
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)