

SACC-CI-M12FS-5CON - Contact insert



1528536

<https://www.phoenixcontact.com/us/products/1528536>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type socket, 5-pos., M12 contact carrier, A-coded, with straight solder connection

Commercial data

Item number	1528536
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF45
Product key	AF3UBX
GTIN	4046356023443
Weight per piece (including packing)	1.36 g
Weight per piece (excluding packing)	1.22 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FS-5CON - Contact insert



1528536

<https://www.phoenixcontact.com/us/products/1528536>

Technical data

Product properties

Product type	Contact insert
Number of positions	5
Coding	A
Thread type	M12

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Contact resistance	$\leq 0.003 \Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Material specifications

Seal material	FKM
Contact material	CuZn
Contact surface material	Au

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 85 °C

Mounting

Mounting type	PCB mounting
---------------	--------------

SACC-CI-M12FS-5CON - Contact insert


1528536

<https://www.phoenixcontact.com/us/products/1528536>



Drawings

Dimensional drawing




SACC-CI-M12FS-5CON - Contact insert

1528536

<https://www.phoenixcontact.com/us/products/1528536>

Dimensional drawing



Installation diagram


SACC-CI-M12FS-5CON - Contact insert

1528536

<https://www.phoenixcontact.com/us/products/1528536>



Schematic diagram




Pin assignment M12 socket, 5-pos., A-coded, socket side view

1528536

<https://www.phoenixcontact.com/us/products/1528536>

Drilling plan/solder pad geometry



SACC-CI-M12FS-5CON - Contact insert



1528536

<https://www.phoenixcontact.com/us/products/1528536>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1528536>

 cUL Recognized Approval ID: E118976				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	60 V	4 A	-	-

 UL Recognized Approval ID: E118976				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	60 V	4 A	-	-

SACC-CI-M12FS-5CON - Contact insert



1528536

<https://www.phoenixcontact.com/us/products/1528536>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FS-5CON - Contact insert



1528536
<https://www.phoenixcontact.com/us/products/1528536>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com