

RC-09S1N8AT0EP - Cable connector



1610581

<https://www.phoenixcontact.com/us/products/1610581>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1610581
Packing unit	8 pc
Minimum order quantity	8 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFC
GTIN	4046356263832
Weight per piece (including packing)	144.21 g
Weight per piece (excluding packing)	138.148 g
Customs tariff number	85366990
Country of origin	DE

RC-09S1N8AT0EP - Cable connector



1610581

<https://www.phoenixcontact.com/us/products/1610581>

Technical data

Notes

Order information:	Order crimp contacts 8 x Ø 1 mm, 1 x Ø 2 mm separately
--------------------	--

Product properties

Product type	Circular connector (cable-side)
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	9
Connection profile	8+1
Coding	N

Connection data

Conductor connection

Connection method	Crimp connection
-------------------	------------------

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
Nominal current I _N	20 A
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.14 mm ²
Max. cross section	0.56 mm ²
Nominal current I _N	8 A
Nominal voltage U _N	48 V AC
	74 V DC

Mechanical properties

Mechanical data

RC-09S1N8AT0EP - Cable connector



1610581

<https://www.phoenixcontact.com/us/products/1610581>

Insertion/withdrawal cycles	50
-----------------------------	----

Connector

Direction of rotation	Standard
-----------------------	----------

Environmental and real-life conditions

Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

RC-09S1N8AT0EP - Cable connector



1610581

<https://www.phoenixcontact.com/us/products/1610581>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-09S1N8AT0EP - Cable connector



1610581

<https://www.phoenixcontact.com/us/products/1610581>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	18aaa6ee-11f9-4808-aff0-869d4e3d0d65

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com