

VS-08-T-RJ45/IP 20 - RJ45 sleeve housing


1688638

<https://www.phoenixcontact.com/us/products/1688638>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

RJ45 sleeve housing IP20, for pin insert VS-08-ST-RJ45, with push-pull interlocking for panel mounting frames, for cable cross section 5.0 mm ... 6.5 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1688638 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | AB10 |
| Product key | ABNAAZ |
| GTIN | 4017918607920 |
| Weight per piece (including packing) | 5.85 g |
| Weight per piece (excluding packing) | 4.87 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

VS-08-T-RJ45/IP 20 - RJ45 sleeve housing

1688638

<https://www.phoenixcontact.com/us/products/1688638>



Technical data

Product properties

| | |
|----------------------|------------------------|
| Product type | Bend protection sleeve |
| Type | RJ45 |
| No. of cable outlets | 1 |
| Cable outlet | straight |

Dimensions

| | |
|--------|---------|
| Width | 29.4 mm |
| Height | 13.8 mm |
| Length | 30.1 mm |

Material specifications

| | |
|--|------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Housing material | PA |

Cable/line

| | |
|-------------------------|---------------|
| External cable diameter | 5 mm ... 6 mm |
|-------------------------|---------------|

Mechanical properties

| | |
|-----------------------------|-------|
| Mechanical data | |
| Insertion/withdrawal cycles | ≥ 750 |

Environmental and real-life conditions

| | |
|---------------------------------|------------------|
| Ambient conditions | |
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 80 °C |

VS-08-T-RJ45/IP 20 - RJ45 sleeve housing

1688638

<https://www.phoenixcontact.com/us/products/1688638>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27440392 |
| ECLASS-13.0 | 27440392 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

VS-08-T-RJ45/IP 20 - RJ45 sleeve housing



1688638

<https://www.phoenixcontact.com/us/products/1688638>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com