

VS-15-ST-DSUB-CD-MG - D-SUB contact support

1688913

<https://www.phoenixcontact.com/us/products/1688913>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, Shell size 2, for 15 signal contacts, pin contact type, for crimp contacts, straight, attachment with M3 thread, for VS-15... panel mounting frames



Commercial data

Item number	1688913
Packing unit	100 pc
Minimum order quantity	10 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4017918823061
Weight per piece (including packing)	12.5 g
Weight per piece (excluding packing)	7.37 g
Customs tariff number	85366990
Country of origin	DE

VS-15-ST-DSUB-CD-MG - D-SUB contact support

1688913

<https://www.phoenixcontact.com/us/products/1688913>



Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Shielded	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

Connection data

Connection method	Crimp connection
-------------------	------------------

Dimensions

Width	18 mm
Height	12.93 mm
Length	39.52 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 3.40 N

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-55 °C ... 130 °C

Mounting

VS-15-ST-DSUB-CD-MG - D-SUB contact support

1688913

<https://www.phoenixcontact.com/us/products/1688913>



Mounting type	Threads

VS-15-ST-DSUB-CD-MG - D-SUB contact support

1688913

<https://www.phoenixcontact.com/us/products/1688913>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1688913>



UL Recognized
Approval ID: E118976

VS-15-ST-DSUB-CD-MG - D-SUB contact support

1688913

<https://www.phoenixcontact.com/us/products/1688913>



Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-15-ST-DSUB-CD-MG - D-SUB contact support

1688913

<https://www.phoenixcontact.com/us/products/1688913>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	95d47bb4-95b2-44b5-be73-2da66d4de2af

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com