

STZ 2-MSTBC-5,08 V0 GN - Strain relief



1710492

<https://www.phoenixcontact.com/us/products/1710492>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Strain relief, color: green, product range: STZ, width: 10 mm

Commercial data

Item number	1710492
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AA08
Product key	AAHZBI
GTIN	4046356078092
Weight per piece (including packing)	0.78 g
Weight per piece (excluding packing)	0.748 g
Customs tariff number	85389099
Country of origin	DE

STZ 2-MSTBC-5,08 V0 GN - Strain relief



1710492

<https://www.phoenixcontact.com/us/products/1710492>

Technical data

Product properties

Product type	Strain relief
Product family	STZ
Number of positions	2
Pitch	5.08 mm

Dimensions

Width	10 mm
Height	3.4 mm
Length	41.3 mm
Pitch	5.08 mm

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

STZ 2-MSTBC-5,08 V0 GN - Strain relief



1710492

<https://www.phoenixcontact.com/us/products/1710492>

Classifications

ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

STZ 2-MSTBC-5,08 V0 GN - Strain relief



1710492

<https://www.phoenixcontact.com/us/products/1710492>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.017 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com