

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Fitted cover for ME upper parts ME...OTP...MSTBO..., width: 20 mm, height: 54 mm, depth: 4.75 mm, color: black (similar RAL 9005)



Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2200415
Packing unit	10 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHAAZ
GTIN	4046356577625
Weight per piece (including packing)	2.15 g
Weight per piece (excluding packing)	2.15 g
Country of origin	DE

ME 22,5 PLATE-MSTBO BK - Insertion plate



2200415

<https://www.phoenixcontact.com/us/products/2200415>

Technical data

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

Dimensions

Width	20 mm
Height	54 mm
Depth	4.75 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Slot
---------------	------

ME 22,5 PLATE-MSTBO BK - Insertion plate



2200415

<https://www.phoenixcontact.com/us/products/2200415>

Classifications

UNSPSC

UNSPSC 21.0	31261501
-------------	----------

ME 22,5 PLATE-MSTBO BK - Insertion plate



2200415

<https://www.phoenixcontact.com/us/products/2200415>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com