

# FLKM-D 9 SUB/S/ZFKDS - Termination board

2302984

<https://www.phoenixcontact.com/us/products/2302984>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Standard 1:1 D-SUB module, with spring-cage connection and D-SUB pin strip, no. of positions 9



## Your advantages

- 9-pos. ... 50-pos.
- Spring-cage connection technology
- In accordance with IEC 60807-2
- 1:1 connection

## Commercial data

Item number	2302984
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C422
Product key	DK2182
GTIN	4017918943950
Weight per piece (including packing)	74.7 g
Weight per piece (excluding packing)	52.58 g
Customs tariff number	85369010
Country of origin	DE

# FLKM-D 9 SUB/S/ZFKDS - Termination board

2302984

<https://www.phoenixcontact.com/us/products/2302984>



## Technical data

### Product properties

Product type	Interface module
Number of positions	9

#### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Oversupply category	II
Pollution degree	2

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 2.5 A
Current (Total current)	≤ 22.5 A

#### Air clearances and creepage distances

Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 µs)

### Connection data

#### Connection 1 (control level)

Connection in acc. with standard	IEC 60807-2
Connection method	D-SUB pin strip
Screw thread	UNC 4-40
Number of connections	1
Number of positions	9
Insertion/withdrawal cycles	> 500
Pitch	2.74 mm

#### Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7 mm
Number of positions	10
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Ferrule without plastic sleeve) 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 12
Pitch	5.08 mm

### Signaling

Status display present	no
------------------------	----

# FLKM-D 9 SUB/S/ZFKDS - Termination board

2302984

<https://www.phoenixcontact.com/us/products/2302984>



## Dimensions

### Item dimensions

Width	33.75 mm
Height	77 mm
Depth	51.27 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP20
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Approvals

UKCA	
Certificate	UKCA-compliant

## Standards and regulations

Air clearances and creepage distances	
Standards/regulations	EN IEC 60664-1

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

# FLKM-D 9 SUB/S/ZFKDS - Termination board


2302984

<https://www.phoenixcontact.com/us/products/2302984>



## Drawings

Circuit diagram



# FLKM-D 9 SUB/S/ZFKDS - Termination board



2302984

<https://www.phoenixcontact.com/us/products/2302984>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2302984>

cUL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		125 V	2.5 A	-	-

UL Recognized		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine		125 V	2.5 A	-	-

# FLKM-D 9 SUB/S/ZFKDS - Termination board

2302984

<https://www.phoenixcontact.com/us/products/2302984>



## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FLKM-D 9 SUB/S/ZFKDS - Termination board

2302984

<https://www.phoenixcontact.com/us/products/2302984>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)