

TP57AT/702000 S00045 - Touch panel



2401398

<https://www.phoenixcontact.com/us/products/2401398>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 14.5 cm / 5.7"-TFT display (analog resistive (polyester)), 320 x 240 pixel(s) (QVGA), 65536 colors, Arm9™, 200 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 6.0, Open platform, without bus system.

Commercial data

Item number	2401398
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRCABA
GTIN	4055626148267

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 6.0
RAM	512 KB SRAM
Data storage system	NOR-Flash, 32 MB

Display

Display type	14.5 cm / 5.7"-TFT
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	40000 h
Color spectrum	65536 colors
Reading angle left	75.00 °
Reading angle right	75.00 °
Reading angle top	60.00 °
Reading angle bottom	75.00 °

Interfaces

Interfaces	2x USB Host 2.0
Optional interfaces	none
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	Open platform
---------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Typical current consumption	0.4 A
-----------------------------	-------

Real-time clock

TP57AT/702000 S00045 - Touch panel



2401398

<https://www.phoenixcontact.com/us/products/2401398>

Realtime clock	Yes
----------------	-----

Supply

Power supply unit	24 V DC $\pm$ 20 %
-------------------	--------------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	168 mm / 126 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	160 mm / 118 mm / 54 mm (Mounting cutout, depth with bus if bus system present in the device)
-------------------------------------	---

TP57AT/702000 S00045 - Touch panel



2401398

<https://www.phoenixcontact.com/us/products/2401398>

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-15 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com