

VISU+ 2 SP SNMP - Visualization software



2404837

<https://www.phoenixcontact.com/us/products/2404837>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Driver license for SNMP-compatible devices. Only in conjunction with a valid Visu+ runtime license including driver connection (Visu+ RT-D).

Commercial data

Item number	2404837
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRDADG
GTIN	4055626458304
Weight per piece (including packing)	39.82 g
Weight per piece (excluding packing)	39.82 g
Country of origin	DE

Technical data

Product properties

Product type	Visualization
Basic functions	Connection via SNMP to all SNMP-compatible devices.

System properties

Intended use for the software	Visualization
-------------------------------	---------------

License information

Type of license	Driver license
-----------------	----------------

Functionality

Basic functions	Connection via SNMP to all SNMP-compatible devices.
Number of I/O nodes	0

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® XP (SP3)
	Windows® Vista Business
	Windows® 7 Professional SP1 (32-Bit/64-Bit)
	Windows® 7 Ultimate SP1 (32-Bit/64-Bit)
	Windows® 8 Professional (32-Bit/64-Bit)
	Windows® 8 Enterprise (32-Bit/64-Bit)
	Windows® Server 2003
	Windows® Server 2008
	Windows® Server 2008 R2
	Windows® 10 (32-Bit/64-Bit)
Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Optical drive	DVD-ROM
Screen resolution	1024 x 768 pixel(s) (XGA)

Classifications

ECLASS

ECLASS-13.0	27242502
-------------	----------

ETIM

ETIM 9.0	EC001416
----------	----------

UNSPSC

UNSPSC 21.0	43231500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com