

# VISU+ 2 SP JETTER - Visualization software



2404840

<https://www.phoenixcontact.com/us/products/2404840>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Driver license for Jetter controllers. Only in conjunction with a valid Visu+ runtime license including driver connection (Visu+ RT-D).

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2404840       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | DRDADG        |
| GTIN                                 | 4055626458335 |
| Weight per piece (including packing) | 39.82 g       |
| Weight per piece (excluding packing) | 39.82 g       |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                 |                                                                  |
|-----------------|------------------------------------------------------------------|
| Product type    | Visualization                                                    |
| Basic functions | Connection via the JetIPCOM7 protocol to all Jetter controllers. |

### System properties

|                               |               |
|-------------------------------|---------------|
| Intended use for the software | Visualization |
|-------------------------------|---------------|

### License information

|                 |                |
|-----------------|----------------|
| Type of license | Driver license |
|-----------------|----------------|

### Functionality

|                     |                                                                  |
|---------------------|------------------------------------------------------------------|
| Basic functions     | Connection via the JetIPCOM7 protocol to all Jetter controllers. |
| Number of I/O nodes | 0                                                                |

### System requirements

|                     |                                             |
|---------------------|---------------------------------------------|
| Operating equipment | Keyboard, mouse                             |
| Operating system    | Windows® XP (SP3)                           |
|                     | Windows® Vista Business                     |
|                     | Windows® 7 Professional SP1 (32-Bit/64-Bit) |
|                     | Windows® 7 Ultimate SP1 (32-Bit/64-Bit)     |
|                     | Windows® 8 Professional (32-Bit/64-Bit)     |
|                     | Windows® 8 Enterprise (32-Bit/64-Bit)       |
|                     | Windows® Server 2003                        |
|                     | Windows® Server 2008                        |
|                     | Windows® Server 2008 R2                     |
|                     | Windows® 10 (32-Bit/64-Bit)                 |
| Hard disk memory    | min. 1 GByte (recommended: 2 GB)            |
| Supported browsers  | Internet Explorer 5.5 or higher             |
| Languages supported | German, English, French, Italian            |
| Optical drive       | DVD-ROM                                     |
| Screen resolution   | 1024 x 768 pixel(s) (XGA)                   |

# VISU+ 2 SP JETTER - Visualization software



2404840

<https://www.phoenixcontact.com/us/products/2404840>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242502 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001416 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43231500 |
|-------------|----------|

Environmental product compliance

EU RoHS

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|-----------------------------------------|-------------------------------------------------------------------------------------|

EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|