

# CABLE-50/4FLK14/22,0M/YUC - Front adapter

2902800

<https://www.phoenixcontact.com/us/products/2902800>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cast Yokogawa front adapter with attached round cable and an injection-molded 50-pos. socket strip for the connection of 4 x 8 channels on the field side. Cable length: 22.0 m

## Your advantages

- Four 14-pos. connectors on the module side for connecting four 8-channel VARIOFACE modules of the system cabling
- Lateral cable outlet of the I/O module

## Commercial data

Item number	2902800
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK222N
GTIN	4046356681025
Weight per piece (including packing)	4,243 g
Weight per piece (excluding packing)	4,240 g
Country of origin	DE

# CABLE-50/4FLK14/22,0M/YUC - Front adapter

2902800

<https://www.phoenixcontact.com/us/products/2902800>



## Technical data

### Product properties

Product type	Front adapter
--------------	---------------

### Electrical properties

Operating voltage (DC)	≤ 30 V DC
Current (Per path, 70°C)	≤ 500 mA

Supported controller YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV151
	ADV551

Supported controller YOKOGAWA STARDOM

Suitable I/O card	NFDV151
	NFDV551

### Connection data

#### Control side

Connection method	Yokogawa, I/O cards compatible
Number of connections	1
Number of positions	50
Tightening torque	0.5 Nm (Screw connection)

#### Field level

Connection method	IDC/FLK socket strip
Number of connections	4
Number of positions	14
Pitch	2.54 mm

### Dimensions

#### Cable

Length	22 m
--------	------

### Cable/line

#### 50X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	50
Shielded	yes
Cable type	50X0.14 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	50x 0.14 mm <sup>2</sup>

# CABLE-50/4FLK14/22,0M/YUC - Front adapter

2902800

<https://www.phoenixcontact.com/us/products/2902800>



Wire diameter incl. insulation	1 mm $\pm 0.03$ mm
External cable diameter	11.00 mm $\pm 0.3$ mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	$\leq 145 \Omega/\text{km}$ (at 20 °C)
Insulation resistance	$\geq 20 \text{ M}\Omega \cdot \text{km}$ (20 °C)
Smallest bending radius, fixed installation	114 mm
Smallest bending radius, movable installation	205 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of $\geq 18x$ outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable)
	UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# CABLE-50/4FLK14/22,0M/YUC - Front adapter

2902800

<https://www.phoenixcontact.com/us/products/2902800>



## Drawings

Connection diagram

50-pos. connector to the I/O card	4 x 14-pos. connector to the module	Wire color
1	Byte 0	1 black
3		2 brown
5		3 red
7		4 orange
9		5 yellow
11		6 green
13		7 blue
15		8 Violet
41		9 gray
39		10 White
17	Byte 1	1 white-black
19		2 white-brown
21		3 white-red
23		4 white-orange
25		5 White-yellow
27		6 white-green
29		7 white-blue
31		8 white-violet
43		9 white-gray
37		10 brown-black
2	Byte 2	1 brown-red
4		2 brown-orange
6		3 brown-yellow
8		4 brown-green
10		5 brown-blue
12		6 brown-violet
14		7 brown-gray
16		8 brown-white
42		9 green-black
36		10 green-brown
18	Byte 3	1 green-red
20		2 green-orange
22		3 green-blue
24		4 green-violet
26		5 green-gray
28		6 green-white
30		7 yellow-black
32		8 yellow-brown
44		9 yellow-red
34		10 yellow-orange

# CABLE-50/4FLK14/22,0M/YUC - Front adapter

2902800

<https://www.phoenixcontact.com/us/products/2902800>



## Classifications

### UNSPSC

UNSPSC 21.0

32151601

# CABLE-50/4FLK14/22,0M/YUC - Front adapter

2902800

<https://www.phoenixcontact.com/us/products/2902800>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)