

# CABLE-KS40/KS40/20M/YUC/CS - Cable



2904443

<https://www.phoenixcontact.com/us/products/2904443>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled round cable with two molded 40-pos. socket strips (1:1 connection). Cable length: 20.0 m

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2904443                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C421                           |
| Product key                          | DK2CZZ                         |
| GTIN                                 | 4055626061863                  |
| Weight per piece (including packing) | 3,884 g                        |
| Weight per piece (excluding packing) | 3,884 g                        |
| Customs tariff number                | 85444290                       |
| Country of origin                    | CN                             |

# CABLE-KS40/KS40/20M/YUC/CS - Cable



2904443

<https://www.phoenixcontact.com/us/products/2904443>

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

### Electrical properties

|                        |                                           |
|------------------------|-------------------------------------------|
| Operating voltage (DC) | ≤ 30 V DC                                 |
| Current (Per path)     | ≤ 500 mA (up to 70°C ambient temperature) |

### Cable/line

|              |      |
|--------------|------|
| Cable length | 20 m |
|--------------|------|

#### 50X0.14 [PVC]

|                                               |                                                                                                                      |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| UL AWM Style                                  | 2464/1061                                                                                                            |
| Number of positions                           | 50                                                                                                                   |
| Shielded                                      | yes                                                                                                                  |
| Cable type                                    | 50X0.14 [PVC]                                                                                                        |
| Conductor type                                | Assembled shielded round cable                                                                                       |
| Conductor structure signal line               | 7x 0.16 mm                                                                                                           |
| AWG signal line                               | 26                                                                                                                   |
| Conductor cross section                       | 50x 0.14 mm <sup>2</sup>                                                                                             |
| Wire diameter incl. insulation                | 1 mm ±0.03 mm                                                                                                        |
| External cable diameter                       | 11.00 mm ±0.3 mm                                                                                                     |
| Outer sheath, material                        | Semi-rigid PVC                                                                                                       |
| External sheath, color                        | gray                                                                                                                 |
| Conductor material                            | Tin-plated Cu litz wires                                                                                             |
| Cable resistance                              | ≤ 145 Ω/km (at 20 °C)                                                                                                |
| Insulation resistance                         | ≥ 20 MΩ*km (20 °C)                                                                                                   |
| Smallest bending radius, fixed installation   | 114 mm                                                                                                               |
| Smallest bending radius, movable installation | 205 mm                                                                                                               |
| Dynamic load capacity (bending)               | Max. bending cycles: 5000 (at a radius of ≥ 18x outside diameter)                                                    |
| Halogen-free                                  | no                                                                                                                   |
| Flame resistance                              | IEC 60332-1-2 (raw cable)<br>VDE 0842, Part 332-1-2 (raw cable)<br>IEC 60332-3-22 (raw cable)<br>UL VW-1<br>CSA FT-1 |
| Resistance to oil                             | can withstand occasional splashes (raw cable)                                                                        |

# CABLE-KS40/KS40/20M/YUC/CS - Cable



2904443

<https://www.phoenixcontact.com/us/products/2904443>

## Connection data

### Field level

|                       |                           |
|-----------------------|---------------------------|
| Connection method     | Yokogawa, KS compatible   |
| Number of connections | 1                         |
| Number of positions   | 40                        |
| Tightening torque     | 0.5 Nm (Screw connection) |

### Controller level

|                       |                                |
|-----------------------|--------------------------------|
| Connection method     | Yokogawa, I/O cards compatible |
| Number of connections | 1                              |
| Number of positions   | 40                             |
| Tightening torque     | 0.5 Nm (Screw connection)      |

## Notes

|                    |                                                                                                                                                                                                                                                                                |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

# CABLE-KS40/KS40/20M/YUC/CS - Cable



2904443

<https://www.phoenixcontact.com/us/products/2904443>

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC000237 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# CABLE-KS40/KS40/20M/YUC/CS - Cable



2904443

<https://www.phoenixcontact.com/us/products/2904443>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)