

UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module intended for use with Honeywell Experion C300 16-channel analog input cards. Channels 13.....16 feature differential inputs.



Your advantages

- These VARIOFACE modules are used in combination with the relevant front adapters
- UM-PRO housing
- DIN rail mounting, includes grounding foot
- LED blown fusing indication
- Per channel shield connection
- Per channel disconnects with test points
- Per channel pluggable 500 mA fusing

Commercial data

Item number	2905245
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218H
GTIN	4046356959377
Weight per piece (including packing)	421.2 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85371098
Country of origin	US

UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	37
No. of channels	16

Electrical properties

Nominal voltage U_N	24 V DC
Max. current carrying capacity per branch	500 mA (fuse limited)

Supported controller HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TAIX01 (non-redundant)
	TAIX11 (redundant)
	TAIX51 (non-redundant)
	TAIX61 (redundant)
	TAIN01 (non-redundant)
	TAIN11 (redundant)

Supported controller HONEYWELL Experion LX Series 8

Suitable I/O card	8X-TAIXA1
	8X-TAIXB1

Connection data

Field level

Connection method	Screw connection with disconnect knife
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

Signaling

Status display	no
Status display present	yes, if the fuse fails

Dimensions

Item dimensions

UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Width	124 mm
Height	142.3 mm
Depth	79 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Notes


General	Standard or halogen-free cables
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

UM-D37M/DS/FU/LED/AID4/C300/L - Termination board

2905245

<https://www.phoenixcontact.com/us/products/2905245>

Drawings




UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Circuit diagram



UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905245>



cUL Recognized

Approval ID: E238705



UL Recognized

Approval ID: E238705

UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UM-D37M/DS/FU/LED/AID4/C300/L - Termination board



2905245

<https://www.phoenixcontact.com/us/products/2905245>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4f25b2db-9463-4fb9-9858-9b7111ae5bf7

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com