

RIF-LVM-100-200 AC/110 DC - Plug-in module



2907058

<https://www.phoenixcontact.com/us/products/2907058>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with varistor and yellow LED, input voltage: 100 V AC ... 200 V AC / 110 V DC $\pm 20\%$, polarity A1-, A2+

Commercial data

Item number	2907058
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	DK6545
GTIN	4055626181196
Weight per piece (including packing)	3.41 g
Weight per piece (excluding packing)	3.041 g
Country of origin	CN

RIF-LVM-100-200 AC/110 DC - Plug-in module



2907058

<https://www.phoenixcontact.com/us/products/2907058>

Technical data

Product properties

Product type	Plug-in module
Product family	RIFLINE complete

Electrical properties

Nominal voltage U_N	110 V DC
	100 V AC ... 200 V AC

Input data

Nominal input voltage U_N	110 V DC
Input voltage range	120 V AC ... 230 V AC

Approvals

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

RIF-LVM-100-200 AC/110 DC - Plug-in module



2907058

<https://www.phoenixcontact.com/us/products/2907058>

Classifications

ETIM

ETIM 8.0	EC002586
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)