

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse, nominal current: 10 A, length: 31.8 mm, diameter: 6.35 mm

Commercial data

Item number	2908358
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM24
Product key	CMUEZ9
GTIN	4055626294773
Weight per piece (including packing)	4.9 g
Weight per piece (excluding packing)	4.8 g
Customs tariff number	85361010
Country of origin	CN

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Technical data

Product properties

Product type	Fuse
--------------	------

Electrical properties

Tripping characteristic	fast-blow
Rated voltage	400 V
Nominal current I_N	10 A

Dimensions

Dimensions	6.2 x 32 mm
------------	-------------

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908358>



EAC

Approval ID: RU C-DE.BL08.B.00724

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Classifications

ECLASS

ECLASS-13.0	27142008
ECLASS-15.0	27142008

ETIM

ETIM 9.0	EC002298
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

FUSE 10A/400V GRL - Fuse

2908358

<https://www.phoenixcontact.com/us/products/2908358>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com