

EMG 45-H 7,5MM KLAR - Covering hood

2946214

<https://www.phoenixcontact.com/us/products/2946214>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm



Commercial data

Item number	2946214
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCBA
GTIN	4017918082178
Weight per piece (including packing)	8.52 g
Weight per piece (excluding packing)	8.52 g
Customs tariff number	39269097
Country of origin	DE

EMG 45-H 7,5MM KLAR - Covering hood

2946214

<https://www.phoenixcontact.com/us/products/2946214>



Technical data

Product properties

Product type	Cover
Housing type	Component housing
Housing series	EMG
Product family	EMG
Number of positions	16
Ventilation openings present	no

Dimensions

Width	45 mm
Depth	75 mm
Length	38 mm

Material specifications

Color (Housing)	transparent
Material	PC
Flammability rating according to UL 94	V2
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions	
Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C

Mounting

Mounting type	Snap in
---------------	---------

EMG 45-H 7,5MM KLAR - Covering hood

2946214

<https://www.phoenixcontact.com/us/products/2946214>



Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG 45-H 7,5MM KLAR - Covering hood

2946214

<https://www.phoenixcontact.com/us/products/2946214>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com