

EMG 12-H 52MM GN - Covering hood



2947129

<https://www.phoenixcontact.com/us/products/2947129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 12.5 mm

Commercial data

Item number	2947129
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC11
Product key	ACHCBA
GTIN	4017918082598
Weight per piece (including packing)	8.09 g
Weight per piece (excluding packing)	8.09 g
Customs tariff number	85369010
Country of origin	DE

EMG 12-H 52MM GN - Covering hood



2947129

<https://www.phoenixcontact.com/us/products/2947129>

Technical data

Product properties

Product type	Cover
Housing type	Component housing
Housing series	EMG
Product family	EMG12
Number of positions	4
Ventilation openings present	no

Dimensions

Width	12.5 mm
Depth	75 mm
Length	38 mm

Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	Polycarbonate, glass-fiber-reinforced
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C

Mounting

Mounting type	Snap in
---------------	---------

EMG 12-H 52MM GN - Covering hood



2947129

<https://www.phoenixcontact.com/us/products/2947129>

Classifications

ETIM

ETIM 8.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG 12-H 52MM GN - Covering hood



2947129

<https://www.phoenixcontact.com/us/products/2947129>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com